



Thermofit<sup>®</sup> Molded Parts  
Specification Control Drawing  
Limited Distribution

Part Number : 562A011 thru 067-25/225  
Description : Transition,  
1 to 4 Cables

NOTES

- 1. All dimensions are in  $\frac{\text{inches}}{\text{[millimeters]}}$  ;  $\frac{\text{lbs}}{\text{[gms]}}$
- 2. Dimensions appearing in table are as follows:
  - a - As Supplied
  - b - After Unrestricted Recovery
- 3. Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.
- 4. Molding ports are optional. When -00 modification number is specified molding ports will be located as shown.



| TABLE OF DIMENSIONS |                |                |                |               |                 |                 |                |                 |                |     |     |               |               |
|---------------------|----------------|----------------|----------------|---------------|-----------------|-----------------|----------------|-----------------|----------------|-----|-----|---------------|---------------|
| PART NUMBER         | H              |                | J,K,L & N      |               | P               | R               | S              | T               | U              | C*  | D*  | HW            | W             |
|                     | Min            | Max            | Min            | Max           | ±10%            | ±10%            | ±10%           | ±10%            | ±10%           | ±5% | ±5% | ±20%          | ±20%          |
|                     | a              | b              | a              | b             | b               | b               | b              | b               | b              | b   | b   | b             | b             |
| 562A011-25/225      | .52<br>[13,2]  | .27<br>[6,9]   | .26<br>[6,6]   | .14<br>[3,4]  | .95<br>[24,1]   | 1.51<br>[38,4]  | .95<br>[24,1]  | 1.73<br>[43,9]  | .71<br>[18,0]  | 45  | 15  | .06<br>[1,52] | .04<br>[1,02] |
| 562A022-25/225      | .76<br>[19,3]  | .38<br>[9,7]   | .37<br>[9,4]   | .21<br>[5,3]  | 1.40<br>[35,6]  | 1.42<br>[36,1]  | 1.26<br>[32,0] | 1.70<br>[43,2]  | .91<br>[23,1]  | 45  | 15  | .07<br>[1,78] | .04<br>[1,02] |
| 562A032-25/225      | .76<br>[19,3]  | .38<br>[9,7]   | .52<br>[13,2]  | .27<br>[6,9]  | 1.94<br>[49,3]  | 1.42<br>[36,1]  | 1.77<br>[45,0] | 1.99<br>[50,5]  | 1.00<br>[25,4] | 45  | 15  | .07<br>[1,78] | .06<br>[1,52] |
| 562A043-25/225      | 1.06<br>[26,9] | .51<br>[13,0]  | .52<br>[13,2]  | .27<br>[6,9]  | 1.94<br>[49,3]  | 2.04<br>[51,8]  | 1.77<br>[45,0] | 2.59<br>[65,8]  | 1.32<br>[33,5] | 45  | 15  | .10<br>[2,54] | .06<br>[1,52] |
| 562A054-25/225      | 1.52<br>[38,6] | .73<br>[18,5]  | .76<br>[19,3]  | .38<br>[9,7]  | 2.83<br>[71,9]  | 2.95<br>[74,9]  | 2.57<br>[65,3] | 3.75<br>[95,3]  | 1.83<br>[46,5] | 45  | 15  | .12<br>[3,05] | .07<br>[1,78] |
| 562A067-25/225      | 2.19<br>[55,6] | 1.05<br>[26,7] | 1.06<br>[26,9] | .51<br>[13,0] | 4.00<br>[101,6] | 4.27<br>[108,5] | 3.64<br>[92,5] | 5.32<br>[135,1] | 2.58<br>[65,5] | 45  | 15  | .18<br>[4,57] | .10<br>[2,54] |

Raychem  
RAYCHEM CORPORATION  
300 CONSTITUTION DRIVE  
MENLO PARK, CALIFORNIA 94025  
(415) 361-6055

Revision : A  
Date : 5/27/93

Part Number : 562A011 thru 067-25/225  
Description : Transition,  
1 to 4 Cables

Thermofit<sup>®</sup> Molded Parts  
Specification Control Drawing  
Limited Distribution

Part Number : 562A011 thru 067-25/225  
Description : Transition,  
1 to 4 Cables

| COMPATABILITY CHART |                            |         |                   |               |                     |
|---------------------|----------------------------|---------|-------------------|---------------|---------------------|
| MATERIAL DASH NO.   | MATERIAL DESCRIPTION       | RT SPEC | COATING SLASH NO. | COATING S NO. | COATING DESCRIPTION |
| -25                 | Elastomer, Fluid Resistant | RT-1325 | /225              | S-1206        | Adhesive            |
|                     |                            |         |                   |               |                     |
|                     |                            |         |                   |               |                     |
|                     |                            |         |                   |               |                     |
|                     |                            |         |                   |               |                     |
|                     |                            |         |                   |               |                     |

If this document is printed it becomes uncontrolled.  
Check for the latest revision.

ORDERING INFORMATION

562A0XX -25 -XX /225

Base part number

Material dash number  
(See Compatability Chart)

Modification number  
(If necessary, see front of scd binder  
for a complete list)

Adhesive slash number  
(If necessary, see Compatability Chart)

THIS DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE; CONSULT YOUR  
NEAREST FIELD REPRESENTATIVE FOR CURRENT REVISION

Raychem  
RAYCHEM CORPORATION  
300 CONSTITUTION DRIVE  
MENLO PARK, CALIFORNIA 94025  
(415) 361-6055

Revision : A  
Date : 5/27/93

Part Number : 562A011 thru 067-25/225  
Description : Transition,  
1 to 4 Cables  
CAD FILE MP93157