





PART NUMBER
10142707-XXLF





PART NUMBER:

10142707-XX LF

PIN COUNT:
02~12 PIN



PIN	DIM A	DIM B
02	8.35	-
04	12.05	5.70
06	17.75	11.40
08	23.45	17.10
10	29.15	22.80
12	34.85	28.50



NOTES:

1. MATERIAL: PA66 UL94V-2, HALOGEN FREE, GLOW WIRE COMPATIBLE.
2. COLOR: BLACK.
3. RoHS COMPLIANT.
4. CRIMP TERMINAL P/N: 10143250.
5. MATE WITH HEADER P/N: 10142708.
6. PRODUCT SPEC: GS-12-1405.
7. PACKAGE SPEC: GS-14-2595.

spec ref				dr	Tony Leng	2017/02/10	projection mm	size	A3	scale	5:2		
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Tony Leng	2018/01/05		ecn no	ELX-N-28879-1				
				chr	-	-							
				appr	Tim Yao	2018/01/09		product family				rel level	Released
surface	linear	0.X	±0.30	Amphenol FCI	title	Minitek Power 5.7 HSG			dwg no	10142707		rev	B
		0.XX	±0.20										
		0.XXX	±0.10										
	angular	0°	±2°	cat. no.	Product - Customer Drw				sheet 1 of 2				

A

B

C


D

A


B

C


D




02P




06P




10P




04P



08P



12P

spec ref				dr		Tony Leng		2017/02/10		projection		mm		size		A3		scale		5:2							
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED				eng		Tony Leng		2018/01/05						ecn no		ELX-N-28879-1									
chr						-		-																			
appr						Tim Yao				2018/01/09		product family				rel level		Released									
surface		linear		0.X		±0.30		Amphenol FCI		title		Minitek Power 5.7 HSG						dwg no		10142707				rev		B	
				0.XX		±0.20																					
				0.XXX		±0.10																					
		angular		0°		±2°				cat. no.		Product - Customer Drw						sheet 2 of 2									