

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0152660751](#)
Status: **Active**
Overview: [Premo-Flex Cable Jumpers](#)
Description: 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 102.00mm Cable Length, Tin (Sn) Plating, 7 Circuits



Series image - Reference only

Documents:

- | | |
|--|--|
| Drawing (PDF) | Datasheet (PDF) |
| Product Specification PS-15266-001-001 (PDF) | RoHS Certificate of Compliance (PDF) |
| Packaging Specification PK-15266-001-001 (PDF) | |

General

Product Family	Cable
Series	15266
Comments	Contacts on the same side, Type A
Crimp Quality Equipment	Yes
Overview	Premo-Flex Cable Jumpers
Product Name	Premo-Flex FFC Jumper
UPC	884982434363

Physical

Cable Length	102.00mm
Circuits (Loaded)	7
Material - Plating Mating	Tin
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-15266-001-001
Product Specification	PS-15266-001-001
Sales Drawing	SD-15266-001

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[15266](#) Series

Mates With

Easy-On FFC/FPC Connector:

[527450733](#) , [527460733](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION