



FCIconnect.com

Copyright FCI

1

2

## List of "SFV\_\_R-3/4STE1" customer document

| DOCUMENT NO. | LIST                                                                                    |
|--------------|-----------------------------------------------------------------------------------------|
| SC-SFV02     | SPEC.                                                                                   |
| JSA92600     | CAT.NO.TABLE FOR 0.5mm CONTACT SPACING CONNECTOR (SFV__R-3/4ST_)                        |
| JSA92601     | CONNECTOR USED FOR FPC WITH 0.5mm CONTACT SPACING (SFV__R-3ST_)                         |
| JSA92602     | CONNECTOR USED FOR FPC WITH 0.5mm CONTACT SPACING (SFV__R-4ST_)                         |
| JSA92603     | CAT.NO.TABLE FOR PLASTIC TAPE PACKAGED 0.5mm CONTACT SPACING CONNECTOR (SFV__R-3/4STE1) |
| JSA92604     | PLASTIC TAPE PACKAGED 0.5mm CONTACT SPACING CONNECTOR (SFV__R-3STE1)                    |
| JSA92605     | PLASTIC TAPE PACKAGED 0.5mm CONTACT SPACING CONNECTOR (SFV__R-4STE1)                    |
| JSA92606     | RECOMMENDED CABLE (FPC) (SFV__R-3/4ST_)                                                 |
| BJM-SFV102   | HANDLING PROCEDURES                                                                     |

|             |  |                |  |                                                         |  |                               |  |                                       |  |                        |  |                                                                             |  |  |  |
|-------------|--|----------------|--|---------------------------------------------------------|--|-------------------------------|--|---------------------------------------|--|------------------------|--|-----------------------------------------------------------------------------|--|--|--|
| mat'l. code |  |                |  | surface<br>ISO 1302 <input checked="" type="checkbox"/> |  | tolerance<br>ISO 406 ISO 1101 |  | projection<br>                        |  | product family<br>58EF |  |                                                                             |  |  |  |
| ltr         |  | ecn no         |  | dr                                                      |  | date                          |  | tolerances unless otherwise specified |  |                        |  | title                                                                       |  |  |  |
| A           |  | J03-0196       |  | H.T                                                     |  | '03/5/1                       |  | angles<br>linear                      |  |                        |  | 0.5mm SPACING FPC CONNECTOR<br>DOCUMENT LIST<br>(Cat. No. : SFV__R-3/4STE1) |  |  |  |
| B           |  | J06-0372       |  | H.T                                                     |  | '06/9/7                       |  |                                       |  |                        |  |                                                                             |  |  |  |
|             |  |                |  |                                                         |  |                               |  | scale $\chi$                          |  |                        |  | dwg no<br>JSA 95809                                                         |  |  |  |
|             |  |                |  |                                                         |  |                               |  |                                       |  |                        |  |                                                                             |  |  |  |
|             |  |                |  |                                                         |  |                               |  | FCI                                   |  |                        |  | sheet 1 of 1<br>size<br>A4                                                  |  |  |  |
|             |  |                |  |                                                         |  |                               |  |                                       |  |                        |  |                                                                             |  |  |  |
|             |  |                |  |                                                         |  |                               |  | type Product Customer Drawing         |  |                        |  | Rev.<br>B                                                                   |  |  |  |
|             |  |                |  |                                                         |  |                               |  |                                       |  |                        |  |                                                                             |  |  |  |
| sheet index |  | revision sheet |  | B<br>1                                                  |  |                               |  |                                       |  |                        |  |                                                                             |  |  |  |

form: A4

1

2

## CAT. NO. &amp; DIMENSIONS

| NO. OF CONTACTS (n) | CAT. NO.       | DIMENSIONS (NOTE2) |         |         |         |
|---------------------|----------------|--------------------|---------|---------|---------|
|                     |                | A ± 0.2            | B ± 0.2 | C ± 0.1 | D ± 0.1 |
| 4                   | SFV 4R-3/4ST__ | 7.5                | 5.9     | 1.5     | 1.6     |
| 5                   | SFV 5R-3/4ST__ | 8.0                | 6.4     | 2.0     | 2.1     |
| 6                   | SFV 6R-3/4ST__ | 8.5                | 6.9     | 2.5     | 2.6     |
| 7                   | SFV 7R-3/4ST__ | 9.0                | 7.4     | 3.0     | 3.1     |
| 8                   | SFV 8R-3/4ST__ | 9.5                | 7.9     | 3.5     | 3.6     |
| 9                   | SFV 9R-3/4ST__ | 10.0               | 8.4     | 4.0     | 4.1     |
| 10                  | SFV10R-3/4ST__ | 10.5               | 8.9     | 4.5     | 4.6     |
| 11                  | SFV11R-3/4ST__ | 11.0               | 9.4     | 5.0     | 5.1     |
| 12                  | SFV12R-3/4ST__ | 11.5               | 9.9     | 5.5     | 5.6     |
| 13                  | SFV13R-3/4ST__ | 12.0               | 10.4    | 6.0     | 6.1     |
| 14                  | SFV14R-3/4ST__ | 12.5               | 10.9    | 6.5     | 6.6     |
| 15                  | SFV15R-3/4ST__ | 13.0               | 11.4    | 7.0     | 7.1     |
| 16                  | SFV16R-3/4ST__ | 13.5               | 11.9    | 7.5     | 7.6     |
| 17                  | SFV17R-3/4ST__ | 14.0               | 12.4    | 8.0     | 8.1     |
| 18                  | SFV18R-3/4ST__ | 14.5               | 12.9    | 8.5     | 8.6     |
| 19                  | SFV19R-3/4ST__ | 15.0               | 13.4    | 9.0     | 9.1     |
| 20                  | SFV20R-3/4ST__ | 15.5               | 13.9    | 9.5     | 9.6     |
| 21                  | SFV21R-3/4ST__ | 16.0               | 14.4    | 10.0    | 10.1    |
| 22                  | SFV22R-3/4ST__ | 16.5               | 14.9    | 10.5    | 10.6    |
| 23                  | SFV23R-3/4ST__ | 17.0               | 15.4    | 11.0    | 11.1    |
| 24                  | SFV24R-3/4ST__ | 17.5               | 15.9    | 11.5    | 11.6    |
| 25                  | SFV25R-3/4ST__ | 18.0               | 16.4    | 12.0    | 12.1    |
| 26                  | SFV26R-3/4ST__ | 18.5               | 16.9    | 12.5    | 12.6    |
| 27                  | SFV27R-3/4ST__ | 19.0               | 17.4    | 13.0    | 13.1    |
| 28                  | SFV28R-3/4ST__ | 19.5               | 17.9    | 13.5    | 13.6    |
| 29                  | SFV29R-3/4ST__ | 20.0               | 18.4    | 14.0    | 14.1    |
| 30                  | SFV30R-3/4ST__ | 20.5               | 18.9    | 14.5    | 14.6    |
| 31                  | SFV31R-3/4ST__ | 21.0               | 19.4    | 15.0    | 15.1    |
| 32                  | SFV32R-3/4ST__ | 21.5               | 19.9    | 15.5    | 15.6    |
| 33                  | SFV33R-3/4ST__ | 22.0               | 20.4    | 16.0    | 16.1    |
| 34                  | SFV34R-3/4ST__ | 22.5               | 20.9    | 16.5    | 16.6    |
| 35                  | SFV35R-3/4ST__ | 23.0               | 21.4    | 17.0    | 17.1    |

CAT. NO.

SFV (n) R - 3 ST \_\_

SERIES NAME

NO. OF CONTACTS

RIGHT ANGLE TYPE

FOR FPC,  
WITH CABLE LOCK MECHANISM

CONTACT DIRECTION

3: LOWER CONTACT TYPE

4: UPPER CONTACT TYPE

FOR AUTOMATIC MOUNTING  
(SMT)

PACKAGE STYLE

## NOTES

1. THIS PRODUCT IS THE CONNECTOR USED FOR FPC AND COPS WITH AUTOMATIC MOUNTING (SMT).
2. SEE PART DRAWINGS FOR DIMENSIONS A~D.
3. THIS PRODUCT IS THE CONNECTOR WITH CABLE LOCK MECHANISM.


|             |          |                |          |                                       |         |                            |                                                                                     |            |           |                                                                                 |              |      |  |
|-------------|----------|----------------|----------|---------------------------------------|---------|----------------------------|-------------------------------------------------------------------------------------|------------|-----------|---------------------------------------------------------------------------------|--------------|------|--|
| mat'l. code |          |                |          | surface ISO 1302 ✓                    |         | tolerance ISO 406 ISO 1101 |                                                                                     | projection |           | product family 58EF                                                             |              |      |  |
| ltr         | ecn no   | dr             | date     | tolerances unless otherwise specified |         |                            |                                                                                     |            |           | title                                                                           |              |      |  |
| 1           | ---      | M.H            | '95/1/18 | angles                                |         | linear                     |                                                                                     | scale X    |           | CAT. NO. TABLE FOR 0.5 mm CONTACT SPACING CONNECTOR (Cat. No. : SFV__R-3/4ST__) |              |      |  |
| 2           | ---      | M.I            | '97/1/15 |                                       |         |                            |                                                                                     |            |           |                                                                                 |              |      |  |
| 3           | J00182   | M.Y            | '00/4/24 |                                       |         |                            |                                                                                     |            |           |                                                                                 |              |      |  |
| AA          | J03-0196 | H.T            | '03/5/1  | dr                                    | 9/17/06 |                            |  |            | dwg no    |                                                                                 | sheet 1 of 1 | size |  |
| AB          | J06-0372 | H.T            | '06/9/7  | engr                                  | 9/17/06 |                            |                                                                                     |            | JSA 92600 |                                                                                 | A4           |      |  |
|             |          |                |          | chr                                   | 9/18/06 |                            |                                                                                     |            |           |                                                                                 |              |      |  |
|             |          |                |          | appd                                  | 9/18/06 |                            |                                                                                     |            |           |                                                                                 |              |      |  |
| sheet index |          | revision sheet | AB 1     | type Product Customer Drawing         |         |                            |                                                                                     |            |           |                                                                                 |              |      |  |

SC-SFV02 JSA92601, 92602, 92603, 92604, 92605, 92606  
form: A4




FCIconnect.com

Copyright FCI




| PT. NO. | PARTS NAME     | MATERIAL                                   | Q'TY | NOTE               |
|---------|----------------|--------------------------------------------|------|--------------------|
| 1       | HOUSING        | POLYAMIDE RESIN GLASS REINFORCED (UL94V-0) | 1    | COLOR: BLACK       |
| 2       | SLIDER         | PPS RESIN GLASS REINFORCED (UL94V-0)       | 1    | COLOR: BLACK       |
| 3       | CONTACT        | PHOSPHOR BRONZE                            | n    | PLATING: TIN ALLOY |
| 4       | MOUNTING PLATE |                                            | 2    |                    |

RECOMMENDED PC BOARD LAYOUT  
(COMPONENT SIDE)PATTERN FOR  
MOUNTING PLATE  
FIXING

n: NO. OF CONTACTS

## NOTES

1. THIS PRODUCT IS THE CONNECTOR USED FOR FPC AND CYPES WITH AUTOMATIC MOUNTING (SMT).
2. THIS PRODUCT IS LOWER CONTACT TYPE CONNECTOR WITH CABLE LOCK MECHANISM.
3. FLATNESS OF CONTACT TERMINAL AND MOUNTING PLATE MUST BE WITHIN TOLERANCE IN E PORTION DETAILED DRAWING.



|             |          |          |           |                                       |                       |                               |        |                                                                                                   |                                                                                     |                                                                                             |           |   |  |  |              |  |  |            |      |                                                                                     |  |  |  |  |  |  |  |  |  |
|-------------|----------|----------|-----------|---------------------------------------|-----------------------|-------------------------------|--------|---------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------|-----------|---|--|--|--------------|--|--|------------|------|-------------------------------------------------------------------------------------|--|--|--|--|--|--|--|--|--|
| mat'l. code |          |          |           | surface<br>ISO 1302 ✓                 |                       | tolerance<br>ISO 406 ISO 1101 |        | projection<br> |                                                                                     | product family<br>58EF                                                                      |           |   |  |  |              |  |  |            |      |                                                                                     |  |  |  |  |  |  |  |  |  |
| ltr         | ecn no   | dr       | date      | tolerances unless otherwise specified |                       |                               |        |                                                                                                   |                                                                                     | title<br>CONNECTOR USED FOR FPC<br>WITH 0.5 mm CONTACT SPACING<br>(Cat. No. : SFV__R-3ST__) |           |   |  |  |              |  |  |            |      |                                                                                     |  |  |  |  |  |  |  |  |  |
| 1           | —        | M.H.     | '94/12/8  | angles                                | linear                | ±0.2                          |        |                                                                                                   |                                                                                     |                                                                                             |           |   |  |  |              |  |  |            |      |  |  |  |  |  |  |  |  |  |  |
| 2           | —        | M.H.     | '95/11/10 |                                       |                       |                               |        |                                                                                                   |                                                                                     |                                                                                             |           |   |  |  |              |  |  |            |      |                                                                                     |  |  |  |  |  |  |  |  |  |
| 3           | J00182   | M.Y.     | '00/4/24  |                                       |                       |                               |        |                                                                                                   |                                                                                     | scale                                                                                       |           | X |  |  |              |  |  |            |      |                                                                                     |  |  |  |  |  |  |  |  |  |
| AA          | J03-0196 | H.T.     | '03/5/1   | dr                                    | <i>H. [signature]</i> |                               | 9/7/66 |                                                                                                   |  |                                                                                             | dwg no    |   |  |  | sheet 1 of 1 |  |  |            | size |                                                                                     |  |  |  |  |  |  |  |  |  |
| AB          | J06-0064 | H.T.     | '06/2/23  | engr                                  | <i>H. [signature]</i> |                               | 9/7/66 |                                                                                                   |                                                                                     |                                                                                             | JSA 92601 |   |  |  | A4           |  |  |            |      |                                                                                     |  |  |  |  |  |  |  |  |  |
| AC          | J06-0372 | H.T.     | '06/9/17  | chr                                   | <i>R. [signature]</i> |                               | 9/8/66 |                                                                                                   |                                                                                     |                                                                                             |           |   |  |  |              |  |  |            |      |                                                                                     |  |  |  |  |  |  |  |  |  |
|             |          |          |           | appd                                  | <i>S. [signature]</i> |                               | 9/4/66 |                                                                                                   |                                                                                     |                                                                                             |           |   |  |  |              |  |  |            |      |                                                                                     |  |  |  |  |  |  |  |  |  |
| sheet index |          | revision |           | AC                                    |                       |                               |        |                                                                                                   |                                                                                     |                                                                                             |           |   |  |  |              |  |  | Rev.<br>AC |      |                                                                                     |  |  |  |  |  |  |  |  |  |

SC-SFV02  
form: A4

JSA92600

1

2




| PT. NO. | PARTS NAME     | MATERIAL                                   | Q'TY | NOTE              |
|---------|----------------|--------------------------------------------|------|-------------------|
| 1       | HOUSING        | POLYAMIDE RESIN GLASS REINFORCED (UL94V-0) | 1    | COLOR:BLACK       |
| 2       | SLIDER         | PPS RESIN GLASS REINFORCED (UL94V-0)       | 1    | COLOR:BLACK       |
| 3       | CONTACT        | PHOSPHOR BRONZE                            | n    | PLATING:TIN ALLOY |
| 4       | MOUNTING PLATE |                                            | 2    |                   |

RECOMMENDED PC BOARD LAYOUT  
(COMPONENT SIDE)

PATTERN FOR  
MOUNTING PLATE  
FIXING

n: NO. OF CONTACTS



#### NOTES

1. THIS PRODUCT IS THE CONNECTOR USED FOR FPC AND COPEs WITH AUTOMATIC MOUNTING (SMT).
2. THIS PRODUCT IS UPPER CONTACT TYPE CONNECTOR WITH CABLE LOCK MECHANISM.
3. FLATNESS OF CONTACT TERMINAL AND MOUNTING PLATE MUST BE WITHIN TOLERANCE IN E PORTION DETAILED DRAWING.

|             |          |                |           |                                       |         |                               |  |            |                               |                                                                                             |                     |  |                            |  |            |  |
|-------------|----------|----------------|-----------|---------------------------------------|---------|-------------------------------|--|------------|-------------------------------|---------------------------------------------------------------------------------------------|---------------------|--|----------------------------|--|------------|--|
| mat'l. code |          |                |           | surface<br>ISO 1302                   |         | tolerance<br>ISO 406 ISO 1101 |  | projection |                               | product family<br>58EF                                                                      |                     |  |                            |  |            |  |
| ltr         | ecn no   | dr             | date      | tolerances unless otherwise specified |         |                               |  | <br>       |                               | title<br>CONNECTOR USED FOR FPC<br>WITH 0.5 mm CONTACT SPACING<br>(Cat. No. : SFV__R-4ST__) |                     |  |                            |  |            |  |
| 1           | —        | M.H            | '94/12/8  | angles                                |         |                               |  |            |                               |                                                                                             |                     |  |                            |  |            |  |
| 2           | —        | M.H            | '95/11/10 | linear                                |         |                               |  |            |                               |                                                                                             |                     |  |                            |  |            |  |
| 3           | J00182   | M.Y            | '00/4/24  |                                       |         |                               |  | scale      |                               |                                                                                             |                     |  |                            |  |            |  |
| AA          | J03-0196 | H.T            | '03/5/1   | dr                                    | 9/12/06 |                               |  |            |                               |                                                                                             | dwg no<br>JSA 92602 |  | sheet 1 of 1<br>size<br>A4 |  |            |  |
| AB          | J06-0064 | H.T            | '06/12/23 | engr                                  | 9/17/06 |                               |  |            |                               |                                                                                             |                     |  |                            |  |            |  |
| AC          | J06-0372 | H.T            | '06/9/17  | chr                                   | 9/8/06  |                               |  |            |                               |                                                                                             |                     |  |                            |  |            |  |
|             |          |                |           | appd                                  | 9/6/06  |                               |  |            | type Product Customer Drawing |                                                                                             |                     |  |                            |  |            |  |
| sheet index |          | revision sheet |           | AC                                    | 1       |                               |  |            |                               |                                                                                             |                     |  |                            |  | Rev.<br>AC |  |

SC-SFV02 JSA92600  
form: A4

## CAT. NO. &amp; DIMENSIONS

| NO. OF CONTACTS (n) | CAT. NO.       | DIMENSIONS (NOTE3) |         |         |
|---------------------|----------------|--------------------|---------|---------|
|                     |                | F ± 5              | G ± 0.3 | H ± 0.1 |
| 4                   | SFV 4R-3/4STE1 | 20.4               | 16      | —       |
| 5                   | SFV 5R-3/4STE1 | 20.4               | 16      | —       |
| 6                   | SFV 6R-3/4STE1 | 20.4               | 16      | —       |
| 7                   | SFV 7R-3/4STE1 | 28.4               | 24      | —       |
| 8                   | SFV 8R-3/4STE1 | 28.4               | 24      | —       |
| 9                   | SFV 9R-3/4STE1 | 28.4               | 24      | —       |
| 10                  | SFV10R-3/4STE1 | 28.4               | 24      | —       |
| 11                  | SFV11R-3/4STE1 | 28.4               | 24      | —       |
| 12                  | SFV12R-3/4STE1 | 28.4               | 24      | —       |
| 13                  | SFV13R-3/4STE1 | 28.4               | 24      | —       |
| 14                  | SFV14R-3/4STE1 | 28.4               | 24      | —       |
| 15                  | SFV15R-3/4STE1 | 28.4               | 24      | —       |
| 16                  | SFV16R-3/4STE1 | 28.4               | 24      | —       |
| 17                  | SFV17R-3/4STE1 | 28.4               | 24      | —       |
| 18                  | SFV18R-3/4STE1 | 28.4               | 24      | —       |
| 19                  | SFV19R-3/4STE1 | 28.4               | 24      | —       |
| 20                  | SFV20R-3/4STE1 | 28.4               | 24      | —       |
| 21                  | SFV21R-3/4STE1 | 28.4               | 24      | —       |
| 22                  | SFV22R-3/4STE1 | 28.4               | 24      | —       |
| 23                  | SFV23R-3/4STE1 | 36.4               | 32      | 28.4    |
| 24                  | SFV24R-3/4STE1 | 36.4               | 32      | 28.4    |
| 25                  | SFV25R-3/4STE1 | 36.4               | 32      | 28.4    |
| 26                  | SFV26R-3/4STE1 | 36.4               | 32      | 28.4    |
| 27                  | SFV27R-3/4STE1 | 36.4               | 32      | 28.4    |
| 28                  | SFV28R-3/4STE1 | 36.4               | 32      | 28.4    |
| 29                  | SFV29R-3/4STE1 | 36.4               | 32      | 28.4    |
| 30                  | SFV30R-3/4STE1 | 36.4               | 32      | 28.4    |
| 31                  | SFV31R-3/4STE1 | 48.4               | 44      | 40.4    |
| 32                  | SFV32R-3/4STE1 | 48.4               | 44      | 40.4    |
| 33                  | SFV33R-3/4STE1 | 48.4               | 44      | 40.4    |
| 34                  | SFV34R-3/4STE1 | 48.4               | 44      | 40.4    |
| 35                  | SFV35R-3/4STE1 | 48.4               | 44      | 40.4    |

CAT. NO.

SFV (n) R - 3 ST E1

SERIES NAME

NO. OF CONTACTS

RIGHT ANGLE TYPE

FOR FPC,  
WITH CABLE LOCK MECHANISM

CONTACT DIRECTION

3: LOWER CONTACT TYPE


4: UPPER CONTACT TYPE

FOR AUTOMATIC MOUNTING  
(SMT)

PACKAGE STYLE

## NOTES


- THIS PRODUCT IS THE CONNECTOR USED FOR FPC AND COPELS WITH AUTOMATIC MOUNTING (SMT).
- THIS CATALOG NO. INDICATES PLASTIC TAPE PACKAGED
- SEE PART DRAWINGS FOR DIMENSIONS F-H.
- THIS PRODUCT IS THE CONNECTOR WITH CABLE LOCK MECHANISM.

|             |          |                |          |                                                      |                         |                                                                                         |  |                                                                                                |  |                                                                                                             |  |              |      |         |
|-------------|----------|----------------|----------|------------------------------------------------------|-------------------------|-----------------------------------------------------------------------------------------|--|------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------------|--|--------------|------|---------|
| mat'l. code |          |                |          | surface <input checked="" type="checkbox"/> ISO 1302 |                         | tolerance <input checked="" type="checkbox"/> ISO 406 <input type="checkbox"/> ISO 1101 |  | projection  |  | product family 58EF                                                                                         |  |              |      |         |
| ltr         | ecn no   | dr             | date     | tolerances unless otherwise specified                |                         |                                                                                         |  |                                                                                                |  | title                                                                                                       |  |              |      |         |
| 1           | —        | M.H            | '95/1/18 | angles                                               |                         | linear                                                                                  |  |             |  | CAT. NO. TABLE FOR PLASTIC TAPE PACKAGED<br>0.5 mm CONTACT SPACING CONNECTOR<br>(Cat. No. : SFV__R-3/4STE1) |  |              |      |         |
| 2           | —        | M.I            | '97/11/5 |                                                      |                         |                                                                                         |  | scale $\propto$                                                                                |  |                                                                                                             |  |              |      |         |
| 3           | J00182   | M.Y            | '00/4/24 |                                                      |                         |                                                                                         |  |                                                                                                |  |                                                                                                             |  |              |      |         |
| AA          | J03-0196 | H.T            | '03/5/1  | dr                                                   | <i>H. Shouji</i> 9/7/06 |                                                                                         |  |             |  | dwg no                                                                                                      |  | sheet 1 of 1 | size |         |
| AB          | J06-0372 | H.T            | '06/9/7  | engr                                                 | <i>H. Shouji</i> 9/7/06 |                                                                                         |  |                                                                                                |  | JSA 92603                                                                                                   |  |              | A4   |         |
|             |          |                |          | chr                                                  | <i>R. Shouji</i> 9/8/06 |                                                                                         |  |                                                                                                |  |                                                                                                             |  |              |      |         |
|             |          |                |          | appd                                                 | <i>S. Oudaw</i> 9/11/06 |                                                                                         |  |                                                                                                |  |                                                                                                             |  |              |      |         |
| sheet index |          | revision sheet | AB 1     |                                                      |                         |                                                                                         |  |                                                                                                |  |                                                                                                             |  |              |      | Rev. AB |

SC-SFV02 JSA92600  
form: A4

1


2






FCIconnect.com

Copyright FCI



# RECOMMENDED CABLE (FPC)



| PT. NO. | PARTS NAME      | MATERIAL                                | THICKNESS (μm) |
|---------|-----------------|-----------------------------------------|----------------|
| 1       | BASE FILM       | POLYIMIDE OR POLYESTER OR EQUAL         | 25             |
| 2       | CONDUCTOR       | COPPER FOIL (PLATING : SOLDER 1μm MIN.) | 35             |
| 3       | OVERLAY         | POLYIMIDE OR POLYESTER OR EQUAL         | —              |
| 4       | SUPPORTING TAPE | POLYESTER OR POLYIMIDE OR EQUAL         | 188            |

## NOTES

1. NO BURR AT EACH PORTION.
2. NO PEELING IN COMMON USE.
3. TOTAL THICKNESS LIMIT OF EACH MATERIAL (INCLUDING ADHESIVE AGENT) IS SPECIFIED.
4. THIS DIMENSION INDICATES THE RANGE FOR 0.3 ± 0.035 CONDUCTOR WIDTH.

|             |          |                |         |                                       |         |                            |  |            |  |                     |              |                                                           |            |
|-------------|----------|----------------|---------|---------------------------------------|---------|----------------------------|--|------------|--|---------------------|--------------|-----------------------------------------------------------|------------|
| mat'l. code |          |                |         | surface ISO 1302 ✓                    |         | tolerance ISO 406 ISO 1101 |  | projection |  | product family 58EF |              |                                                           |            |
| ltr         | ecn no   | dr             | date    | tolerances unless otherwise specified |         |                            |  |            |  | <br>                |              | title<br>RECOMMENDED CABLE<br>(Cat. No. : SFV__R-3/4ST__) |            |
| AA          | J03-0196 | H.T            | '03/5/1 |                                       |         |                            |  |            |  |                     |              |                                                           |            |
| AB          | J06-0372 | H.T            | '06/9/7 | angles                                | linear  |                            |  |            |  | scale X             |              | dwg no                                                    |            |
|             |          |                |         | dr                                    | 9/7/06  |                            |  |            |  |                     | sheet 1 of 1 |                                                           | size<br>A4 |
|             |          |                |         | engr                                  | 9/7/06  |                            |  |            |  |                     | JSA 92606    |                                                           |            |
|             |          |                |         | chr                                   | 9/8/06  |                            |  |            |  |                     |              |                                                           |            |
|             |          |                |         | appd                                  | 9/10/06 |                            |  |            |  |                     |              |                                                           |            |
| sheet index |          | revision sheet | AB 1    | type Product Customer Drawing         |         |                            |  |            |  |                     |              |                                                           |            |

SC-SFV02 JSA92600  
form: A4