




REV.	DATE	ECR NO.	DESCRIPTION
A	04/05/03	—	UPDATE DRAWING FORMAT
B	08/04/08	—	REVISE PART DESCRIPTION FROM "JACK" TO "PLUG"



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
8						DRAWN	GRS	08/04/08						
7						CHECKED				PART DESCRIPTION TNC R/A CRIMP PLUG – LMR 400 CABLE (FOR BELDEN 9913, 9914)				
6	COVER	BRASS	NICKEL	1		ISSUED								
5	FERRULE	COPPER	NICKEL	1		SHEET	1 OF 1			PART NO. 122416				
4	GASKET	RUBBER	RED	1										
3	CONTACT PIN	BRASS	GOLD	1					DWG. NO. 122416.DWG					
2	INSULATOR	PTFE	NATURAL	1	CAD FILE C:/122/122416.DWG			REV.						B
1	HOUSING/BODY	BRASS	NICKEL	1										
DESCRIPTION					MATERIAL	FINISH	QTY							