


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	MAXIMUM BUNDLE DIAMETER	PACKAGE QUANTITY	LENGTH = L ± .3 [7]
MLT2LH-LP316	2.0" [51]	50	7.9" [201]
MLT4LH-LP316	4.0" [102]	50	14.3" [362]
MLT6LH-LP316	6.0" [152]	50	20.5" [521]
MLT8LH-LP316	8.0" [203]	50	26.8" [679]




NOTES:

1. APPLICATION TOOLS - GS4MT,PPTMT,ST2MT,ST3MT,HTMT
2. MINIMUM LOOP TENSILE STRENGTH - 250 LBS (1112 NEWTONS) WHEN TESTED ON A 1 1/2" MANDREL.
3. BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
4. TOLERANCES:
.XXX = ±.010 [.25] .XX = ±.02 [.5]
.X = ±.03 [.8] ANGLES = ±2°

FULLY ROUNDED
EDGES ALONG
STRAP BODY

SECTION A - A
SCALE: 8x

04A	3/13	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO	SSECN01037
03A	2/12	MIM	RGRO	---	NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY	-----
02	8/04	JAMB	DPN	JJB	Ⓒ REMOVED "AISI" NO. 1 FULL RADIUSED" & REPLACED WITH "FULLY ROUNDED"	-----
01	11/03	JAMB	DPN	JJB	Ⓐ ADDED APPLICATION TOOL ST3MT" Ⓑ REMOVED "316" DESIGNATION FROM PANDUIT I.D.	11292
00	6/03	JAMB	DPN	JJB	DRAWING RELEASED	10544
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE				METAL LOCKING TIE LIGHT-HEAVY SERIES 316 STAINLESS STEEL	
ITEM REVISION NAME				CUSTOMER DRAWING	
N41127BS/04				PANDUIT	
DATASET FILE NAME					
N41127BS/04				MATERIAL:	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .1 [2.54] .XXX ± .005 [.127] .XX ± .01 [.25] ANGLES ± 5 °  THIRD ANGLE PROJECTION				316 STAINLESS STEEL	
				DRAWING NUMBER:	
N41127BS_DC					
DRAWN BY	DATE	CHK	SCALE	SIZE	
JAMB	6/03	DPN	2:1	SHT 1 OF 1	
				A	