





SFC-120-T2-L-D-A



SFC-110-T1-L-D-A

SFC-135-T2-L-D-A-K



SFC SERIES

COST SAVING RELIABLE SOCKET

RA[®] **CSA**[®]
FILE NO. E111594 FILE NO. 090871 Q 000





Slotted SMT tails

*Alignment
pin option*



Polarized

SFC	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	D	OPTION
04, 05, 10, 15, 20, 25, 30, 35, 40, 45, 50 (Standard sizes)			-T1 = Through-hole Tiger Eye™ LITE -T2 = Surface Mount Tiger Eye™ LITE	-F = Gold flash on contact, Matte Tin on tail -L = 10µ" (0,25 µm) Gold on contact, Matte Tin on tail		-A = Alignment Pin -K = (4,00 mm) .157" DIA Polyimide film Pick & Place Pad -TR = Tape & Reel (-T2 only)



Note: Some sizes, styles and options are non-standard, non-returnable.