



AC Power Inlet with Fuseholder



Series 4707 for "cold" connections 70°C, protection Class 1 (with ground pin). Terminals are 6.3 × 0.8 mm or 4.8 × 0.8 mm quick-connect or solder. Approved by UL, CSA, and VDE up to 10 amps 250 volts.

Stock No.	Mfr.'s Type	Mounting	Fusing	Terminals	D × H × W (mm)	EACH	
						1-24	25-Up
509-2001	4707.1000	Screw-on	1-pole	Quick-connect, 6.3 × 0.8 mm	41.0 × 34 × 44	16.02	11.64
509-2003	4707.2000	Screw-on	2-pole	Quick-connect, 6.3 × 0.8 mm	41.0 × 34 × 44	16.02	11.64
509-2005	4707.2100	Screw-on	2-pole	Quick-connect, 4.8 × 0.8 mm	31.7 × 34 × 44	16.02	11.64
509-2011	4707.1300	Screw-on	1-pole	Solder	37.6 × 34 × 44	16.02	11.64
509-2013	4707.2300	Screw-on	2-pole	Solder	37.6 × 34 × 44	16.02	11.64


AC Line Filter with AC Inlet



Series 5110 for "cold" connections 65°C, protection class I. Terminals are 6.3 × 0.8 mm quick-connect. Screw-on or snap-in panel mounting. Approved up to 15 A/250 V.

Stock No.	Mfr.'s Type	Fig.	Mounting	Filter (Amps)	Leakage Current	D × H × W (mm)	EACH	
							1-24	25-Up
509-3200	5110.0133.1	1	Screw-on	1 A, Standard	<0.5 mA	55 × 21 × 48	11.61	10.08
509-3202	5110.0333.1	1	Screw-on	3 A, Standard	<0.5 mA	55 × 21 × 48	11.61	10.08
509-3204	5110.0633.1	1	Screw-on	6 A, Standard	<0.5 mA	55 × 21 × 48	11.61	10.08
509-3206	5110.0833.1	1	Screw-on	8 A, Standard	<0.5 mA	55 × 21 × 48	11.61	10.08
509-3208	5110.1033.1	1	Screw-on	10 A, Standard	<0.5 mA	55 × 21 × 48	11.61	10.08
509-3210	5110.1533.1	1	Screw-on	15 A, Standard	<0.5 mA	55 × 21 × 48	11.61	10.08
509-3212	5110.0143.1	2	Snap-in	1 A, Standard	<0.5 mA	55 × 21 × 36	11.61	10.08
509-3214	5110.0343.1	2	Snap-in	3 A, Standard	<0.5 mA	55 × 21 × 36	11.61	10.08
509-3216	5110.0643.1	2	Snap-in	6 A, Standard	<0.5 mA	55 × 21 × 36	11.61	10.08
509-3218	5110.0843.1	2	Snap-in	8 A, Standard	<0.5 mA	55 × 21 × 36	11.61	10.08
509-3219	5110.1043.1	2	Snap-in	10 A, Standard	<0.5 mA	55 × 21 × 36	11.61	10.08
509-3220	5110.1543.1	2	Snap-in	15 A, Standard	<0.5 mA	55 × 21 × 36	11.96	10.38
509-3222	5110.0133.3	1	Screw-on	1 A, Medical	<5.0 µA	55 × 21 × 48	11.61	10.08
509-3224	5110.0333.3	1	Screw-on	3 A, Medical	<5.0 µA	55 × 21 × 48	11.61	10.08
509-3226	5110.0633.3	1	Screw-on	6 A, Medical	<5.0 µA	55 × 21 × 48	11.61	10.08
509-3228	5110.0833.3	1	Screw-on	8 A, Medical	<5.0 µA	55 × 21 × 48	11.61	10.08
509-3230	5110.1033.3	1	Screw-on	10 A, Medical	<5.0 µA	55 × 21 × 48	16.21	14.06
509-3232	5110.1533.3	1	Screw-on	15 A, Medical	<5.0 µA	55 × 21 × 48	11.61	10.08
509-3234	5110.0143.3	2	Snap-in	1 A, Medical	<5.0 µA	55 × 21 × 36	11.61	10.08
509-3236	5110.0343.3	2	Snap-in	3 A, Medical	<5.0 µA	55 × 21 × 36	11.61	10.08
509-3238	5110.0643.3	2	Snap-in	6 A, Medical	<5.0 µA	55 × 21 × 36	11.61	10.08
509-3240	5110.0843.3	2	Snap-in	8 A, Medical	<5.0 µA	55 × 21 × 36	11.61	10.08
509-3242	5110.1043.3	2	Snap-in	10 A, Medical	<5.0 µA	55 × 21 × 36	11.96	10.38
509-3244	5110.1543.3	2	Snap-in	15 A, Medical	<5.0 µA	55 × 21 × 36	11.61	10.08

High Current Line Filter — 20 A




Series C20F for cold connections 65°C, Protection Class I. Screw mount, solder/quick connect terminals 6.3 × 0.8 mm. RFI filter in medical or standard. UL, CSA approved 20 A/125V. VDE approved 16 A/250 V.

Stock No.	Mfr.'s Type	Filter (Amps)	Leakage Current	D × H × W (mm)	EACH	
					1-24	25-Up
509-5070	C20F.0001	20 A / 16A Standard	<0.5 mA	80.8 × 53 × 30	22.17	18.14
509-5072	C20F.0002	20 A / 16A Medical	<5.0 µA	80.8 × 53 × 30	22.17	18.14

509-5074. 0888.0220. Cordset; C19 plug mates to C20 inlet; NEMA 5-15P end. 1-24.....EACH 24.29
25-Up.....EACH 19.43


Filtered AC Inlet/Circuit Breaker for Equipment



Series PEM 45 power entry module combines an AC inlet, circuit breaker for equipment, and optional RFI filter. The circuit breaker provides manual reset of the circuit, 1 or 2-pole thermal overload protection, or no bi-metal for on/off switching only (white switch I/O embossed lettering). Optional undervoltage release. Approved by UL, CSA up to 15 amps at 125 and 250 volt, and VDE up to 10 amps 250 volt.

Stock No.	Mfr.'s Type	Fig.	Overload Protection	Rated Current CBE/Filter	Leakage Current	D × H × W (mm)	EACH	
							1-24	25-Up
509-3246	5-ABTWFO50C0-511	3	1-pole	5 A/6 A	<0.5 mA	51.7 × 91.5 × 36	26.34	18.17
509-3248	5-ABTWFI150C0-811	3	1-pole	15 A/15 A	<0.5 mA	51.7 × 91.5 × 36	27.13	18.71
509-3250	5-ABTWFO50C0-531	3	1-pole	5 A/6 A	<5.0 µA	51.7 × 91.5 × 36	26.34	18.17
509-3252	5-ABTWFI150C0-831	3	1-pole	15 A/15 A	<5.0 µA	51.7 × 91.5 × 36	29.66	20.46
509-3254	5-ABDWFO50C0-511	3	2-pole	5 A/5 A	<0.5 mA	51.7 × 91.5 × 36	29.66	20.46
509-3256	5-ABDWFI150C0-811	3	2-pole	15 A/15 A	<0.5 mA	51.7 × 91.5 × 36	29.66	20.46
509-3258	5-ABDWFO50C0-531	3	2-pole	5 A/5 A	<5.0 µA	51.7 × 91.5 × 36	29.66	20.46
509-3260	5-ABDWFI150C0-831	3	2-pole	15 A/15 A	<5.0 µA	51.7 × 91.5 × 36	30.55	21.07

AC Line Filters with Fuseholders




Series KFA for cold connections 65°C. Protection Class I. Quick connect terminals 6.3 × 0.8mm. Available 2 pos. voltage selector 115/230 or without and with medical or standard RFI filter. Approved up to 10 A/250 V. Fusedrawers ordered separately below.

Stock No.	Mfr.'s Type	Fig.	Fusing	Voltage Selector	Filter (Amps)	Leakage Current	D × H × W (mm)	EACH	
								1-24	25-Up
509-3266	4301.5011	4	1-pole	—	1 A Standard	<0.5 mA	60 × 34 × 44	19.25	13.69
509-3268	4301.5014	4	1-pole	—	6 A Standard	<0.5 mA	60 × 34 × 44	19.25	13.69
509-3270	4301.5015	4	1-pole	—	10 A Standard	<0.5 mA	60 × 34 × 44	19.25	13.69
509-3272	4301.5051	5	1-pole	2 pos.	1 A Standard	<0.5 mA	69 × 34 × 44	21.44	15.25
509-3274	4301.5054	5	1-pole	2 pos.	6 A Standard	<0.5 mA	69 × 34 × 44	21.44	15.25
509-3276	4301.5055	5	1-pole	2 pos.	10 A Standard	<0.5 mA	69 × 34 × 44	21.44	15.25
509-3278	4301.5001	4	2-pole	—	1 A Standard	<0.5 mA	60 × 34 × 44	19.43	13.82
509-3280	4301.5004	4	2-pole	—	6 A Standard	<0.5 mA	60 × 34 × 44	19.43	13.82
509-3282	4301.5005	4	2-pole	—	10 A Standard	<0.5 mA	60 × 34 × 44	19.43	13.82
509-3284	4301.5041	5	2-pole	2 pos.	1 A Standard	<0.5 mA	69 × 34 × 44	22.49	16.00
509-5044	4301.5044	5	2-pole	2 pos.	6 A Standard	<0.5 mA	69 × 34 × 44	19.37	16.91
509-3288	4301.5045	5	2-pole	2 pos.	10 A Standard	<0.5 mA	69 × 34 × 44	22.49	16.00
509-9984	4301.5203	4	2-pole	—	2 A Medical	<5.0 µA	60 × 34 × 44	25.69	18.27
509-3292	4301.5205	4	2-pole	—	4 A Medical	<5.0 µA	60 × 34 × 44	25.69	18.27
509-3294	4301.5241	5	2-pole	2 pos.	1 A Medical	<5.0 µA	69 × 34 × 44	26.96	19.17
509-3296	4301.5243	5	2-pole	2 pos.	2 A Medical	<5.0 µA	69 × 34 × 44	26.96	19.17
509-3298	4301.5245	5	2-pole	2 pos.	4 A Medical	<5.0 µA	69 × 34 × 44	26.96	19.17
509-3299	4301.5247	5	2-pole	2 pos.	6 A Medical	<5.0 µA	69 × 34 × 44	26.96	19.17
509-3300	4301.5249	5	2-pole	2 pos.	10 A Medical	<5.0 µA	69 × 34 × 44	26.96	19.17

Fuse Drawers (Order Fuses Separately)
509-3302. 4301.1224.06. 1 pole, 5 × 20 mm with voltage selector, black.....EACH 3.90
509-3304. 4301.1407. 1-pole, 5 × 20 mm without voltage selector, black.....EACH 1.91
509-3306. 4301.1024.06. 2 pole, 5 × 20 mm with voltage selector, black.....EACH 5.60
509-3308. 4301.1403. 2-pole, 5 × 20 mm without voltage selector, black.....EACH 3.29

AC Line Filters with On/Off Switch



Series KFB for cold connections 65°C, Protection Class I. Quick connect terminals 6.3 × 0.8 mm. Available with medical or standard RFI filter 1 or 2-pole. Approved up to 10 A/250 V.

Stock No.	Mfr.'s Type	Fig.	Switch	Filter (Amps)	Leakage Current	D × H × W (mm)	EACH	
							1-24	25-Up
509-3310	4302.5001	6	1-pole	1 A Standard	<0.5 mA	60 × 31.2 × 44	29.23	20.79
509-3312	4302.5003	6	1-pole	4 A Standard	<0.5 mA	60 × 31.2 × 44	29.23	20.79
509-3314	4302.5004	6	1-pole	6 A Standard	<0.5 mA	60 × 31.2 × 44	29.23	20.79
509-3316	4302.5005	6	1-pole	10 A Standard	<0.5 mA	60 × 31.2 × 44	29.23	20.79
509-3318	4302.5311	7	2-pole	1 A Standard	<0.5 mA	59 × 59 × 27.2	33.88	24.10
509-3320	4302.5313	7	2-pole	4 A Standard	<0.5 mA	59 × 59 × 27.2	33.88	24.10
509-3322	4302.5314	7	2-pole	6 A Standard	<0.5 mA	59 × 59 × 27.2	33.88	24.10
509-3324	4302.5315	7	2-pole	10 A Standard	<0.5 mA	59 × 59 × 27.2	33.88	24.10
509-3326	4302.5331	7	2-pole	1 A Medical	<5.0 µA	59 × 59 × 27.2	33.88	24.10
509-3328	4302.5335	7	2-pole	4 A Medical	<5.0 µA	59 × 59 × 27.2	33.88	24.10
509-3330	4302.5337	7	2-pole	6 A Medical	<5.0 µA	59 × 59 × 27.2	33.88	24.10
509-3332	4302.5339	7	2-pole	10 A Medical	<5.0 µA	59 × 59 × 27.2	33.88	24.10