



MATERIALS:

Body: Brass, Tarnish Resistant Plating

Alloy 360, 1/2 Hard or Phosphor Bronze

Male Contact: Gold Plated Brass

Female Contact: Gold Plated Beryllium Copper

Dielectric: PTFE

Finish:

Body and Fittings: Tarnish resistant

Male and Female Contact – Gold plated

Marking: "POMONA 4958"

RATINGS:

Operating Temperature: -65°C (-85°F) to +165°C (+329°F)

Operating Voltage: 500 VRMS Max.

Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 4958

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02"$ (.51 mm), .xxx = $\pm .005"$ (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[4958](#)