


PROD 4092 CODE	LOC DF	DIST 50	P	F	REVISIONS				
					ZONE	LTR	DESCRIPTION	DATE	APPD
					N	ADD -28 & REDRAW PER DF-3848	CCT	9-90	DE
					P	REACTIVATE 2--5;DF-6614	CT	8-92	SG
					R	REACTIVATE -6;DF-6670	CT	9-92	SG
			✓	✓	S	REV PER 0600-8002-98	JB	02-15-99	ML

PART NO.	A	1
846291-1	12.00	[304.8]
846291-2	16.00	[406.4]
846291-3	24.00	[609.6]
846291-4	36.00	[914.4]
846291-5	96.00	[2438.4]
846291-6	72.00	[1828.8]
846291-7	60.00	[1524.0]
846291-8	7.00	[177.8]
846291-9	8.50	[215.9]
1-846291-0	10.00	[254.0]
1-846291-1	18.00	[457.2]
1-846291-2	396.00	[10058.4]
1-846291-3	15.00	[381.0]
1-846291-4	8.00	[203.2]
1-846291-5	9.00	[228.6]
1-846291-6	20.00	[508.0]
1-846291-7	79.00	[2006.6]
1-846291-8	30.00	[762.0]
1-846291-9	23.50	[596.9]
2-846291-0	17.00	[431.8]
2-846291-1	787.00	[19989.8]
2-846291-2	80.00	[2032.0]
2-846291-3	10.25	[260.3]
2-846291-4	137.00	[3479.8]
2-846291-5	14.00	[355.6]
2-846291-6	40.00	[1016.0]
2-846291-7	48.00	[1219.2]
2-846291-8	236.25	[6000.7]



1. TOLERANCE OF LEAD LENGTH:
UP TO 24 INCHES [609.6] = ±.12 [±3.0]
24 INCHES [609.6] & UP = ±1%
2. MARKED PER MIL-STD-130.
3. OPERATING VOLTAGE: 50 KVDC AT 0 TO 70,000 FEET, -55°C TO 125°C.
4. TO MATE WITH WITH AMP LGH-4
RECEPTACLE WITH 2.00 [50.80] BARREL DEPTH.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES [mm] TOLERANCES ON : 2 PLC DEC ± .02 [0.5] 3 PLC DEC ± - ANGLES ± -	DR 9-27-90 C.C.THOMAS	AMP AMP INCORPORATED Harrisburg, Pa. 17105		
	CHK 9-28-90 D.EABY			
	MATERIAL	APPD 9-28-90 D.EABY	NAME LEAD ASY , DBL . END , LGH-4	
SEE CALLOUTS	APPD 9-28-90 C.THOMAS			
FINISH SEE CALLOUTS	PRODUCT SPEC -	SIZE C		
	APPLICATION SPEC -			
	WEIGHT -	DRAWING NO 846291		
		SCALE 1:1		SHEET 1 OF 1