



TERMINATED VIEW



- 1
- UL RATED 94V-0 THERMOPLASTIC, COLOR: BLACK.
- 2
- PHOSPHOR BRONZE PER QQ-B-750.
- 3
- PLATED WITH .000030 GOLD ON LOCALIZED GOLD PLATE AREA, .000100 - .000200 BRIGHT TIN LEAD ON TERMINATION END, ALL OVER .000050 NICKEL ON ENTIRE CONTACT.
- 4
- POLARIZING FEATURE DOES NOT EXIST ON SAME END AS THE POSN #1 INDICATOR ON 10 AND 14 POSN PRODUCT.
- 5
- UL RATED 94V-1 OR BETTER, THERMOPLASTIC, GRAY.



DETAIL Z
SCALE 10:1
TYPICAL

OBSOLETE	1	.925	1.700	1.980	1.750	35	36	3-746288-4
OBSOLETE	5	1.125	2.100	2.380	2.150	43	44	3-746288-3
OBSOLETE	5	1.275	2.400	2.680	2.450	49	50	3-746288-0
OBSOLETE	5	1.025	1.900	2.180	1.950	39	40	2-746288-9
OBSOLETE	5	.875	1.600	1.880	1.650	33	34	2-746288-8
OBSOLETE	5	.525	.900	1.180	.950	19	20	2-746288-4
OBSOLETE	5	.275	.400	.680	.450	9	10	2-746288-1
	1	1.125	2.100	2.380	2.150	43	44	1-746288-3
	1	1.625	3.100	3.380	3.150	63	64	1-746288-2
	1	1.525	2.900	3.180	2.950	59	60	1-746288-1
	1	1.275	2.400	2.680	2.450	49	50	1-746288-0
	1	1.025	1.900	2.180	1.950	39	40	746288-9
	1	.875	1.600	1.880	1.650	33	34	746288-8
	1	.775	1.400	1.680	1.450	29	30	746288-7
	1	.675	1.200	1.480	1.250	25	26	746288-6
	1	.625	1.100	1.380	1.150	23	24	746288-5
	1	.525	.900	1.180	.950	19	20	746288-4
	1	.425	.700	.980	.750	15	16	746288-3
	1	.375	.600	.880	.650	13	14	746288-2
	1	.275	.400	.680	.450	9	10	746288-1

		MATERIAL		E	D	C	B	A	NO OF POSN	PART NUMBER
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON : DECIMALS ± .005 ANGLES ± 5°		CONTRACT NO			AMP AMP INCORPORATED Harrisburg, Pa. NAME RECEPTACLE KIT, AMP-LATCH NOVO, CTR & MIL PLZN,30 GOLD DUPLEX CONTACTS,W/O STRAIN RLF					
		DR								
		CHK								
		W.E. ZELKO								
MATERIAL MOLDED PARTS: SEE TABLE		APPD			DUPLX CONTACTS,W/O STRAIN RLF					
		APPD								
CONTACTS: 2		D.HOFFMAN								
FINISH		DSGN APPD			SIZE	FSCM NO		DRAWING NO		
		OTHER APPD			D	00779		746288		
CONTACTS: 3					SCALE		NTS		SHEET 1 of 1	