







RECOMMENDED HOLE LAYOUT FOR .070(1.78) MAX. THICK P.C. BOARD

VIEWED FROM COMPONENT SIDE



8 CKT SHOWN

CIRCUIT SIZE	DIM. "A"	DIM. "B"	DIM. "C"
2	—	.21 (5.4)	.370 (9.40)
4	.17 (4.2)	.38 (9.6)	.535 (13.60)
6	.33 (8.4)	.54 (13.8)	.701 (17.80)
8	.50 (12.6)	.71 (18.0)	.866 (22.00)
10	.66 (16.8)	.87 (22.2)	1.031 (26.20)
12	.83 (21.0)	1.04 (26.4)	1.197 (30.40)
14	.99 (25.2)	1.20 (30.6)	1.362 (34.60)
16	1.16 (29.4)	1.37 (34.8)	1.528 (38.80)
18	1.32 (33.6)	1.54 (39.0)	1.693 (43.00)
20	1.49 (37.8)	1.70 (43.2)	1.858 (47.20)
22	1.65 (42.0)	1.87 (47.4)	2.024 (51.40)
24	1.82 (46.2)	2.03 (51.6)	2.189 (55.60)

NOTES:

1) HOUSING MATERIAL:

"BLANK" - NYLON, UNFILLED U.L. 94V-2, COLOR: NATURAL.

210 - NYLON, UNFILLED U.L. 94V-0, COLOR: NATURAL.

BL - NYLON, UNFILLED U.L. 94V-2, COLOR: BLACK.

400 - NYLON, UNFILLED U.L. 94V-0, COLOR: BLACK.

TERMINAL MATERIAL: BRASS

2) TERMINAL PLATING:

"BLANK" - .000035/(.00090) MIN. REFLOWED MATTE TIN OVER .000020/(.00050) MIN. COPPER, (PREPLATE) (FINISH IS BRIGHT IN APPEARANCE, THICKNESS AS APPLIED PRIOR TO REFLOW)

GS - .000030/(.00076) MIN. SELECT GOLD .000100/(.00254) MIN. SELECT MATTE TIN OVER .000050/(.00127) MIN. NICKEL OVERALL.

GS2 - .000015/(.00038) MIN. SELECT GOLD AND .000100/(.00254) MIN. SELECT MATTE TIN OVER .000050/(.00127) MIN. NICKEL OVERALL.

S - .000100/(.00254) MIN. BRIGHT TIN OVER .000050/(.00127) MIN. NICKEL OVERALL.

MS - .000100/(.00254) MIN. MATTE TIN OVER .000050/(.00127) MIN. NICKEL OVERALL.

3) PRODUCT SPECIFICATION: PS-5556-001

4) PACKAGING: SEE CHARTS

5) PART MATES WITH MINI-FIT JR. RECEPTACLE #5557.

6) MOUNTING OPTIONS:

"BLANK" - NO MOUNTING (SEE SD-5566-002 DWG.)
2 - PEG MOUNT

7) PART CONFORMS TO CLASS "B" REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002

8) ANTI-SHINGLING RIB MAY OR MAY NOT APPEAR ON HOUSINGS.

9) CONNECTORS ARE NOT TO BE MATED OR UNMATED WHILE CIRCUITS ARE LIVE.

10) PARTS ARE NOT DESIGNED FOR CURRENT SHARING.

LEGEND:

5566 - N * * * * *

BASE NUMBER

CIRCUIT SIZE

ASSEMBLY TYPE
A - W/O DRAIN HOLES
B - WITH DRAIN HOLES

MOUNTING OPTION (SEE NOTE 6.)

PLATING (SEE NOTE 2.)

HOUSING MAT'L. (SEE NOTE 1.)

PACKAGING
BLANK = TRAY

ADD MATTE P/N'S EC NO: UCP2018-0208 DRWN: ZHARPER CHKD: APPR: FSMITH R8	DESCRIPTION 2017/08/16	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION				
				mm	INCH	DRAWN BY RJF	DATE 8/19/87	TITLE MINI-FIT JR. VERTICAL HEADER ASSEMBLIES WITH MOUNTING PEGS					
			4 PLACES	± ---	± ---	CHECKED BY GT	DATE 8/19/87						
			3 PLACES	± ---	± .015	APPROVED BY FSMITH		DATE 2012/01/10	molex MOLEX INCORPORATED				
			2 PLACES	± 0.38	± .020								
			1 PLACE	± 0.50	± ---	MATERIAL NO.		DOCUMENT NO.	SHEET NO.				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE SHTS 2-4		SDA-5566-N*2*-*					1 OF 4			
			SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									

	13	12	11	10	9	8	7	6	5	4	3	2	1				
J	PLATING:		35 M.I. TIN		PLATING:		35 M.I. TIN		PLATING:		30 M.I. GOLD		PLATING:		30 M.I. GOLD		
	DRAIN HOLES:		WITHOUT DRAIN HOLES		DRAIN HOLES:		WITHOUT DRAIN HOLES		DRAIN HOLES:		WITHOUT DRAIN HOLES		DRAIN HOLES:		WITHOUT DRAIN HOLES		
	MTG. OPTION:		WITH PEGS		MTG. OPTION:		WITH PEGS		MTG. OPTION:		WITH PEGS		MTG. OPTION:		WITH PEGS		
	HOUSING MAT'L:		NYLON 6/6 94V-2 NATURAL		HOUSING MAT'L:		NYLON 6/6 94V-0 NATURAL		HOUSING MAT'L:		NYLON 6/6 94V-2 NATURAL		HOUSING MAT'L:		NYLON 6/6 94V-0 NATURAL		
	PACKAGING:		PK-5566-001		PACKAGING:		PK-5566-001		PACKAGING:		PK-5566-001		PACKAGING:		PK-5566-001		
I	PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS		
	39-29-9023	5566 -02A2	2		39-29-9027	5566 -02A2-210	2		39-29-9025	5566 -02A2GS	2		39-29-9029	5566 -02A2GS-210	2		
	39-29-9043	5566 -04A2	4		39-29-9047	5566 -04A2-210	4		39-29-9045	5566 -04A2GS	4		39-29-9049	5566 -04A2GS-210	4		
	39-29-9063	5566 -06A2	6		39-29-9067	5566 -06A2-210	6		39-29-9065	5566 -06A2GS	6		39-29-9069	5566 -06A2GS-210	6		
	39-29-9083	5566 -08A2	8		39-29-9087	5566 -08A2-210	8		39-29-9085	5566 -08A2GS	8		39-29-9089	5566 -08A2GS-210	8		
H	39-29-9103	5566 -10A2	10		39-29-9107	5566 -10A2-210	10		39-29-9105	5566 -10A2GS	10		39-29-9109	5566 -10A2GS-210	10		
	39-29-9123	5566 -12A2	12		39-29-9127	5566 -12A2-210	12		39-29-9125	5566 -12A2GS	12		39-29-9129	5566 -12A2GS-210	12		
	39-29-9143	5566 -14A2	14		39-29-9147	5566 -14A2-210	14		39-29-9145	5566 -14A2GS	14		39-29-9149	5566 -14A2GS-210	14		
	39-29-9163	5566 -16A2	16		39-29-9167	5566 -16A2-210	16		39-29-9165	5566 -16A2GS	16		39-29-9169	5566 -16A2GS-210	16		
	39-29-9183	5566 -18A2	18		39-29-9187	5566 -18A2-210	18		39-29-9185	5566 -18A2GS	18		39-29-9189	5566 -18A2GS-210	18		
	39-29-9203	5566 -20A2	20		39-29-9207	5566 -20A2-210	20		39-29-9205	5566 -20A2GS	20		39-29-9209	5566 -20A2GS-210	20		
	39-29-9223	5566 -22A2	22		39-29-9227	5566 -22A2-210	22		39-29-9225	5566 -22A2GS	22		39-29-9229	5566 -22A2GS-210	22		
	39-29-9243	5566 -24A2	24		39-29-9247	5566 -24A2-210	24		39-29-9245	5566 -24A2GS	24		39-29-9249	5566 -24A2GS-210	24		
		-				-				-				-			
		-				-				-				-			
G	PLATING:		35 M.I. TIN		PLATING:		35 M.I. TIN		PLATING:		30 M.I. GOLD		PLATING:		30 M.I. GOLD		
	DRAIN HOLES:		WITH DRAIN HOLES		DRAIN HOLES:		WITH DRAIN HOLES		DRAIN HOLES:		WITH DRAIN HOLES		DRAIN HOLES:		WITH DRAIN HOLES		
	MTG. OPTION:		WITH PEGS		MTG. OPTION:		WITH PEGS		MTG. OPTION:		WITH PEGS		MTG. OPTION:		WITH PEGS		
	HOUSING MAT'L:		NYLON 6/6 94V-2 NATURAL		HOUSING MAT'L:		NYLON 6/6 94V-0 NATURAL		HOUSING MAT'L:		NYLON 6/6 94V-2 NATURAL		HOUSING MAT'L:		NYLON 6/6 94V-0 NATURAL		
	PACKAGING:		PK-5566-001		PACKAGING:		PK-5566-001		PACKAGING:		PK-5566-001		PACKAGING:		PK-5566-001		
F	PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS		
		5566 -02B2	2			5566 -02B2-210	2			5566 -02B2GS	2			5566 -02B2GS-210	2		
	39-29-9042	5566 -04B2	4		39-29-9046	5566 -04B2-210	4		39-29-9044	5566 -04B2GS	4		39-28-9048	5566 -04B2GS-210	4		
	39-29-9062	5566 -06B2	6		39-29-9066	5566 -06B2-210	6		39-29-9064	5566 -06B2GS	6		39-28-9068	5566 -06B2GS-210	6		
	39-29-9082	5566 -08B2	8		39-29-9086	5566 -08B2-210	8		39-29-9084	5566 -08B2GS	8		39-28-9088	5566 -08B2GS-210	8		
E	39-29-9102	5566 -10B2	10		39-29-9106	5566 -10B2-210	10		39-29-9104	5566 -10B2GS	10		39-28-9108	5566 -10B2GS-210	10		
	39-29-9122	5566 -12B2	12		39-29-9126	5566 -12B2-210	12		39-29-9124	5566 -12B2GS	12		39-28-9128	5566 -12B2GS-210	12		
	39-29-9142	5566 -14B2	14		39-29-9146	5566 -14B2-210	14		39-29-9144	5566 -14B2GS	14		39-28-9148	5566 -14B2GS-210	14		
	39-29-9162	5566 -16B2	16		39-29-9166	5566 -16B2-210	16		39-29-9164	5566 -16B2GS	16		39-28-9168	5566 -16B2GS-210	16		
	39-29-9182	5566 -18B2	18		39-29-9186	5566 -18B2-210	18		39-29-9184	5566 -18B2GS	18		39-28-9188	5566 -18B2GS-210	18		
D	39-29-9202	5566 -20B2	20		39-29-9206	5566 -20B2-210	20		39-29-9204	5566 -20B2GS	20		39-28-9208	5566 -20B2GS-210	20		
	39-29-9222	5566 -22B2	22			5566 -22B2-210	22		39-29-9224	5566 -22B2GS	22			5566 -22B2GS-210	22		
	39-29-9242	5566 -24B2	24		39-29-9246	5566 -24B2-210	24		39-29-9244	5566 -24B2GS	24		39-28-9248	5566 -24B2GS-210	24		
		-				-				-				-			
		-				-				-				-			
C																	
B																	
A																	

	13		12		11		10		9		8		7		6		5		4		3		2		1			
J																											J	
	PLATING:		100 M.I. BRIGHT TIN		PLATING:		100 M.I. BRIGHT TIN		PLATING:		15 M.I. SELECT GOLD		PLATING:		15 M.I. SELECT GOLD								15 M.I. SELECT GOLD					
	DRAIN HOLES:		WITHOUT DRAIN HOLES		DRAIN HOLES:		WITHOUT DRAIN HOLES		DRAIN HOLES:		WITHOUT DRAIN HOLES		DRAIN HOLES:		WITHOUT DRAIN HOLES								WITHOUT DRAIN HOLES					
	MTG. OPTION:		WITH PEGS		MTG. OPTION:		WITH PEGS		MTG. OPTION:		WITH PEGS		MTG. OPTION:		WITH PEGS								WITH PEGS					
	HOUSING MAT'L:		NYLON 6/6 94V-2 NATURAL		HOUSING MAT'L:		NYLON 6/6 94V-0 NATURAL		HOUSING MAT'L:		NYLON 6/6 94V-2 NATURAL		HOUSING MAT'L:		NYLON 6/6 94V-0 NATURAL								NYLON 6/6 94V-0 NATURAL					
PACKAGING:		PK-5566-001		PACKAGING:		PK-5566-001		PACKAGING:		PK-5566-001		PACKAGING:		PK-5566-001		PACKAGING:		PK-5566-001						PK-5566-001				
I	PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS	I
	39-30-6025	5566 -02A2S	2		39-30-6026	5566 -02A2S-210	2		39-30-0026	5566 -02A2GS2	2		39-30-0027	5566 -02A2GS2-210	2		39-30-0027	5566 -02A2GS2-210	2		39-30-0027	5566 -02A2GS2-210	2		39-30-0027	5566 -02A2GS2-210		
	39-30-6045	5566 -04A2S	4		39-30-6046	5566 -04A2S-210	4		39-30-0046	5566 -04A2GS2	4		39-30-0047	5566 -04A2GS2-210	4		39-30-0047	5566 -04A2GS2-210	4		39-30-0047	5566 -04A2GS2-210	4		39-30-0047	5566 -04A2GS2-210		
	39-30-6065	5566 -06A2S	6		39-30-6066	5566 -06A2S-210	6		39-30-0066	5566 -06A2GS2	6		39-30-0067	5566 -06A2GS2-210	6		39-30-0067	5566 -06A2GS2-210	6		39-30-0067	5566 -06A2GS2-210	6		39-30-0067	5566 -06A2GS2-210		
	39-30-6085	5566 -08A2S	8		39-30-6086	5566 -08A2S-210	8		39-30-0086	5566 -08A2GS2	8		39-30-0087	5566 -08A2GS2-210	8		39-30-0087	5566 -08A2GS2-210	8		39-30-0087	5566 -08A2GS2-210	8		39-30-0087	5566 -08A2GS2-210		
H	39-30-6105	5566 -10A2S	10		39-30-6106	5566 -10A2S-210	10		39-30-0106	5566 -10A2GS2	10		39-30-0107	5566 -10A2GS2-210	10		39-30-0107	5566 -10A2GS2-210	10		39-30-0107	5566 -10A2GS2-210	10		39-30-0107	5566 -10A2GS2-210	H	
	39-30-6125	5566 -12A2S	12		39-30-6126	5566 -12A2S-210	12		39-30-0126	5566 -12A2GS2	12		39-30-0127	5566 -12A2GS2-210	12		39-30-0127	5566 -12A2GS2-210	12		39-30-0127	5566 -12A2GS2-210	12		39-30-0127	5566 -12A2GS2-210		
	39-30-6145	5566 -14A2S	14		39-30-6146	5566 -14A2S-210	14		39-30-0146	5566 -14A2GS2	14		39-30-0147	5566 -14A2GS2-210	14		39-30-0147	5566 -14A2GS2-210	14		39-30-0147	5566 -14A2GS2-210	14		39-30-0147	5566 -14A2GS2-210		
	39-30-6165	5566 -16A2S	16		39-30-6166	5566 -16A2S-210	16		39-30-0166	5566 -16A2GS2	16		39-30-0167	5566 -16A2GS2-210	16		39-30-0167	5566 -16A2GS2-210	16		39-30-0167	5566 -16A2GS2-210	16		39-30-0167	5566 -16A2GS2-210		
	39-30-6185	5566 -18A2S	18		39-30-6186	5566 -18A2S-210	18		39-30-0186	5566 -18A2GS2	18		39-30-0187	5566 -18A2GS2-210	18		39-30-0187	5566 -18A2GS2-210	18		39-30-0187	5566 -18A2GS2-210	18		39-30-0187	5566 -18A2GS2-210		
G	39-30-6205	5566 -20A2S	20		39-30-6206	5566 -20A2S-210	20		39-30-0206	5566 -20A2GS2	20		39-30-0207	5566 -20A2GS2-210	20		39-30-0207	5566 -20A2GS2-210	20		39-30-0207	5566 -20A2GS2-210	20		39-30-0207	5566 -20A2GS2-210	G	
	39-30-6225	5566 -22A2S	22		39-30-6226	5566 -22A2S-210	22		39-30-0226	5566 -22A2GS2	22		39-30-0227	5566 -22A2GS2-210	22		39-30-0227	5566 -22A2GS2-210	22		39-30-0227	5566 -22A2GS2-210	22		39-30-0227	5566 -22A2GS2-210		
	39-30-6245	5566 -24A2S	24		39-30-6246	5566 -24A2S-210	24		39-30-0246	5566 -24A2GS2	24		39-30-0247	5566 -24A2GS2-210	24		39-30-0247	5566 -24A2GS2-210	24		39-30-0247	5566 -24A2GS2-210	24		39-30-0247	5566 -24A2GS2-210		
		-				-				-				-				-				-				-		
		-				-				-				-				-				-				-		
F	PLATING:		100 M.I. BRIGHT TIN		PLATING:		100 M.I. BRIGHT TIN		PLATING:		100 M.I. MATTE TIN		PLATING:		100 M.I. MATTE TIN													F
	DRAIN HOLES:		WITH DRAIN HOLES		DRAIN HOLES:		WITH DRAIN HOLES		DRAIN HOLES:		WITHOUT DRAIN HOLES		DRAIN HOLES:		WITHOUT DRAIN HOLES													
	MTG. OPTION:		WITH PEGS		MTG. OPTION:		WITH PEGS		MTG. OPTION:		WITH PEGS		MTG. OPTION:		WITH PEGS													
	HOUSING MAT'L:		NYLON 6/6 94V-2 NATURAL		HOUSING MAT'L:		NYLON 6/6 94V-0 NATURAL		HOUSING MAT'L:		NYLON 6/6 94V-2 NATURAL		HOUSING MAT'L:		NYLON 6/6 94V-0 NATURAL													
	PACKAGING:		PK-5566-001		PACKAGING:		PK-5566-001		PACKAGING:		PK-5566-001		PACKAGING:		PK-5566-001													
E	PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS	E
	39-30-6047	5566 -02B2S	2		39-30-6048	5566 -02B2S-210	2		46999-0612	5566 -02A2MS	2		46999-0621	5566 -02A2MS-210	2		46999-0621	5566 -02A2MS-210	2		46999-0621	5566 -02A2MS-210	2		46999-0621	5566 -02A2MS-210		
	39-30-6067	5566 -06B2S	6		39-30-6068	5566 -06B2S-210	6		50-34-8559	5566 -06A2MS	6		50-34-8562	5566 -06A2MS-210	6		50-34-8562	5566 -06A2MS-210	6		50-34-8562	5566 -06A2MS-210	6		50-34-8562	5566 -06A2MS-210		
	39-30-6087	5566 -08B2S	8		39-30-6088	5566 -08B2S-210	8		46999-0613	5566 -08A2MS	8		50-34-8563	5566 -08A2MS-210	8		50-34-8563	5566 -08A2MS-210	8		50-34-8563	5566 -08A2MS-210	8		50-34-8563	5566 -08A2MS-210		
	39-30-6107	5566 -10B2S	10		39-30-6108	5566 -10B2S-210	10		46999-0614	5566 -10A2MS	10		46999-0622	5566 -10A2MS-210	10		46999-0622	5566 -10A2MS-210	10		46999-0622	5566 -10A2MS-210	10		46999-0622	5566 -10A2MS-210		
D	39-30-6127	5566 -12B2S	12		39-30-6128	5566 -12B2S-210	12		46999-0615	5566 -12A2MS	12		46999-0623	5566 -12A2MS-210	12		46999-0623	5566 -12A2MS-210	12		46999-0623	5566 -12A2MS-210	12		46999-0623	5566 -12A2MS-210	D	
	39-30-6147	5566 -14B2S	14		39-30-6148	5566 -14B2S-210	14		46999-0616	5566 -14A2MS	14		50-34-8561	5566 -14A2MS-210	14		50-34-8561	5566 -14A2MS-210	14		50-34-8561	5566 -14A2MS-210	14		50-34-8561	5566 -14A2MS-210		
	39-30-6167	5566 -16B2S	16		39-30-6168	5566 -16B2S-210	16		46999-0617	5566 -16A2MS	16		46999-0624	5566 -16A2MS-210	16		46999-0624	5566 -16A2MS-210	16		46999-0624	5566 -16A2MS-210	16		46999-0624	5566 -16A2MS-210		
	39-30-6187	5566 -18B2S	18		39-30-6188	5566 -18B2S-210	18		46999-0618	5566 -18A2MS	18		50-34-8564	5566 -18A2MS-210	18		50-34-8564	5566 -18A2MS-210	18		50-34-8564	5566 -18A2MS-210	18		50-34-8564	5566 -18A2MS-210		
	39-30-6207	5566 -20B2S	20		39-30-6208	5566 -20B2S-210	20		50-34-8560	5566 -20A2MS	20		50-34-2357	5566 -20A2MS-210	20		50-34-2357	5566 -20A2MS-210	20		50-34-2357	5566 -20A2MS-210	20		50-34-2357	5566 -20A2MS-210		
C	39-30-6227	5566 -22B2S	22		39-30-6228	5566 -22B2S-210	22		46999-0619	5566 -22A2MS	22		46999-0625	5566 -22A2MS-210	22		46999-0625	5566 -22A2MS-210	22		46999-0625	5566 -22A2MS-210	22		46999-0625	5566 -22A2MS-210	C	
	39-30-6247	5566 -24B2S	24		39-30-6248	5566 -24B2S-210	24		46999-0620	5566 -24A2MS	24		50-34-8566	5566 -24A2MS-210	24		50-34-8566	5566 -24A2MS-210	24		50-34-8566	5566 -24A2MS-210	24		50-34-8566	5566 -24A2MS-210		
		-				-				-				-				-				-				-		
		-				-				-				-				-				-				-		
		-				-				-				-				-				-				-		
B																											B	
A																											A	

		13		12		11		10		9		8		7		6		5		4		3		2		1	
J		PLATING:		35 M.I. TIN		PLATING:								PLATING:						PLATING:							
		DRAIN HOLES:		WITHOUT DRAIN HOLES		DRAIN HOLES:								DRAIN HOLES:						DRAIN HOLES:							
		MTG. OPTION:		WITH PEGS		MTG. OPTION:								MTG. OPTION:						MTG. OPTION:							
		HOUSING MAT'L:		NYLON 6/6 94V-2 (BLACK)		HOUSING MAT'L:								HOUSING MAT'L:						HOUSING MAT'L:							
		PACKAGING:		PK-5566-001		PACKAGING:								PACKAGING:						PACKAGING:							
		PART NO.	ENG NO.	CKTS		PART NO.	ENG NO.	CKTS						PART NO.	ENG NO.			CKTS		PART NO.	ENG NO.					CKTS	
			-				-								-						-						
I		39-31-9048	5566	-04A2-BL	4																						
			-				-																				
		39-31-9088	5566	-08A2-BL	8																						
			-				-																				
			-				-																				
			-				-																				
H			-				-																				
			-				-																				
			-				-																				
			-				-																				
			-				-																				
			-				-																				
			-				-																				
			-				-																				
			-				-																				
			-				-																				
G		PLATING:				PLATING:		100 M.I. MATTE TIN						PLATING:						PLATING:							
		DRAIN HOLES:				DRAIN HOLES:		WITHOUT DRAIN HOLES						DRAIN HOLES:						DRAIN HOLES:							
		MTG. OPTION:				MTG. OPTION:		WITH PEGS						MTG. OPTION:						MTG. OPTION:							
		HOUSING MAT'L:				HOUSING MAT'L:		NYLON 6/6 94V-0 BLACK						HOUSING MAT'L:						HOUSING MAT'L:							
		PACKAGING:				PACKAGING:		PK-5566-001						PACKAGING:						PACKAGING:							
		PART NO.	ENG NO.		CKTS	PART NO.	ENG NO.	CKTS						PART NO.	ENG NO.			CKTS		PART NO.	ENG NO.					CKTS	
F			-			46999-0335	5566-02A2MS-400	2							-						-						
			-			46999-0336	5566-04A2MS-400	4							-						-						
			-			46999-0337	5566-06A2MS-400	6							-						-						
			-			46999-0338	5566-08A2MS-400	8							-						-						
			-			46999-0339	5566-10A2MS-400	10							-						-						
			-			46999-0340	5566-12A2MS-400	12							-						-						
E			-			46999-0341	5566-14A2MS-400	14							-						-						
			-			46999-0342	5566-16A2MS-400	16							-						-						
			-			46999-0343	5566-18A2MS-400	18							-						-						
			-			46999-0344	5566-20A2MS-400	20							-						-						
			-			46999-0345	5566-22A2MS-400	22							-						-						
			-			46999-0346	5566-24A2MS-400	24							-						-						
D			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						
			-				-								-						-						