




GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

mat'l. code		surface	tolerance	projection	product family
ISO 1302		ISO 406	ISO 1001		D-SUB
lfr		tolerances unless otherwise specified		title	
J	EX-17859	MP	2014/06/06	MM	MALE CONNECTOR DELTA-D US
		angles	linear	scale	RIGHT ANGLED PRESS FIT
		0°±2°	.00±0.1	2:1	
		dr	PESSON	1995/10/27	dwg no
		engr	MITHUN PAUL	2014/06/06	sheet 1 of 1
		chr	ALIAS BABU	2014/06/06	C01-8646-0408
		appd	BIJU K PAUL	2014/06/06	A3
sheet	revision	J			Product Customer Drawing
index	sheet	1			

TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D+0.25	E±0.07	G	PART NUMBER
09	30.81	24.99	18.00	16.79	10.96	5.90 +0.15	D09P80C4G*00 D09P80C6G*00
15	39.14	33.32	26.32	25.12	19.18	5.90 +0.15	D15P80C4G*00 D15P80C6G*00
25	53.03	47.04	40.04	38.84	33.12	5.70 +0.25	D25P80C4G*00 D25P80C6G*00
37	69.32	63.50	56.50	55.30	49.68	5.70 +0.25	D37P80C4G*00 D37P80C6G*00
							Gold flash 0.76 » gold

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D+0.25	E±0.07	G	PART NUMBER
09	30.81	24.99	18.00	16.79	10.96	5.90 +0.15	D09P80C4G*00LF D09P80C6G*00LF
15	39.14	33.32	26.32	25.12	19.18	5.90 +0.15	D15P80C4G*00LF D15P80C6G*00LF
25	53.03	47.04	40.04	38.84	33.12	5.70 +0.25	D25P80C4G*00LF D25P80C6G*00LF
37	69.32	63.50	56.50	55.30	49.68	5.70 +0.25	D37P80C4G*00LF D37P80C6G*00LF
							Gold flash 0.76 » gold