


DIMENSIONS: In



• Molded in Natural Acetal



Mouser Stock Num	Description	Shank	A	H	Length
561-RIV001	RIV 1	0.085±0.005	0.143±0.005	0.058±0.005	0.125±0.015
561-RIV002	RIV 2	0.085±0.005	0.143±0.005	0.058±0.005	0.188±0.015
561-RIV003	RIV 3	0.085±0.005	0.143±0.005	0.058±0.005	0.250±0.015
561-RIV004	RIV 4	0.085±0.005	0.143±0.005	0.058±0.005	0.313±0.015
561-RIV005	RIV 5	0.085±0.005	0.143±0.005	0.058±0.005	0.375±0.015
561-RIV006	RIV 6	0.085±0.005	0.143±0.005	0.058±0.005	0.438±0.015
561-RIV007	RIV 7	0.085±0.005	0.143±0.005	0.058±0.005	0.500±0.015
561-RIV011	RIV 11	125±0.005	0.250±0.005	0.068±0.005	0.125±0.015
561-RIV012	RIV 12	125±0.005	0.250±0.005	0.068±0.005	0.188±0.015
561-RIV013	RIV 13	125±0.005	0.250±0.005	0.068±0.005	0.250±0.015
561-RIV014	RIV 14	125±0.005	0.250±0.005	0.068±0.005	0.313±0.015
561-RIV015	RIV 15	125±0.005	0.250±0.005	0.068±0.005	0.375±0.015
561-RIV016	RIV 16	125±0.005	0.250±0.005	0.068±0.005	0.438±0.015
561-RIV017	RIV 17	125±0.005	0.250±0.005	0.068±0.005	0.500±0.015
561-RIV018	RIV 18	125±0.005	0.250±0.005	0.068±0.005	0.563±0.015
561-RIV019	RIV 19	125±0.005	0.250±0.005	0.068±0.005	0.625±0.015
561-RIV020	RIV 20	125±0.005	0.250±0.005	0.068±0.005	0.688±0.015
561-RIV021	RIV 21	125±0.005	0.218±0.005	0.090±0.005	0.125±0.015
561-RIV022	RIV 22	125±0.005	0.218±0.005	0.090±0.005	0.188±0.015
561-RIV023	RIV 23	125±0.005	0.218±0.005	0.090±0.005	0.250±0.015
561-RIV024	RIV 24	125±0.005	0.218±0.005	0.090±0.005	0.313±0.015
561-RIV025	RIV 25	125±0.005	0.218±0.005	0.090±0.005	0.375±0.015
561-RIV026	RIV 26	125±0.005	0.218±0.005	0.090±0.005	0.500±0.015
561-RIV050	RIV 50	125±0.005	0.218±0.005	0.051±0.005	0.250±0.015
561-RIV055	RIV 55	125±0.005	0.218±0.005	0.051±0.005	0.375±0.015

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

EPD-200702