


HEYCO

Heyco® Nylon Conduit Fittings Flexilok

For Flexible, Corrugated Nylon Conduit/Tubing



FITS CONDUIT NOMINAL SIZE	PART NO. Black	DESCRIPTION	THREAD SIZE	PART DIMENSIONS							
				A		B		C		D	
				Thread		Max		Max O.A.		Clearance	
				Length		Diameter		Length		Hole	
				in.	mm.	in.	mm.	in.	mm.	in.	mm.
PG Hubs											
13	F8772	PG9 13mm FLK13-PG9	PG9	.39	10,0	.80	20,4	1.59	40,5	.60	15,2
16	F8774	PG9 16mm FLK16-PG9	PG9	.39	10,0	.90	22,9	1.65	42,0	.73	18,5
13	F8776	PG11 13mm FLK13-PG11	PG11	.39	10,0	.80	20,4	1.59	40,5	.60	15,2
16	F8778	PG11 16mm FLK16-PG11	PG11	.39	10,0	.90	22,9	1.65	42,0	.73	18,5
16	F8780	PG13 16mm FLK16-PG13	PG13,5	.39	10,0	.90	22,9	1.65	42,0	.80	20,3
21	F8782	PG13 21mm FLK21-PG13	PG13,5	.43	11,0	1.12	28,5	1.76	44,6	.89	22,6
16	F8784	PG16 16mm FLK16-PG16	PG16	.39	10,0	.90	22,9	1.71	43,4	.80	20,3
21	F8786	PG16 21mm FLK21-PG16	PG16	.43	11,0	1.12	28,5	1.81	46,0	.89	22,6
28	F8788	PG21 28mm FLK28-PG21	PG21	.47	12,0	1.43	36,3	1.99	50,6	1.12	28,5
34	F8790	PG29 34mm FLK34-PG29	PG29	.47	12,0	1.69	43,0	2.11	53,6	1.47	37,3
Metric Hubs											
13	F8802	M16 13mm FLKN13-M16	M16 x 1,5	.45	11,5	.80	20,4	1.65	42,0	.63	16,0
16	F8804	M16 16mm FLKN16-M16	M16 x 1,5	.45	11,5	.90	22,9	1.72	43,6	.79	20,1
13	F8806	M20 13mm FLKN13-M20	M20 x 1,5	.55	14,0	.80	20,4	1.75	44,5	.63	16,0
16	F8808	M20 16mm FLKN16-M20	M20 x 1,5	.55	14,0	.90	22,9	1.81	46,0	.79	20,1
20	F8810	M20 20mm FLKN20-M20	M20 x 1,5	.55	14,0	1.09	27,6	1.92	48,7	.79	20,1
21	F8812	M20 21mm FLKN21-M20	M20 x 1,5	.55	14,0	1.12	28,5	1.92	48,7	.79	20,1
25	F8814	M25 25mm FLKN25-M25	M25 x 1,5	.59	15,0	1.28	32,6	2.06	52,3	.99	25,2
28	F8816	M25 28mm FLKN28-M25	M25 x 1,5	.59	15,0	1.43	36,3	2.12	53,8	.99	25,2
34	F8818	M32 34mm FLKN34-M32	M32 x 1,5	.63	16,0	1.69	43,0	2.26	57,5	1.26	32,0



- One piece fast fit allows for quick installation.
- Slim-line design is a space saver.
- No threading of the conduit/tubing is required to install.
- For use with Heyco Nylon Corrugated Conduit/Tubing. See pages 2-21 and 2-22.
- Low fire hazard. Halogen, sulfur, and phosphorus free.
- IP 66 rating—protection against dust and water penetration.
- Suitable for use with both coarse and/or fine pitch conduit/tubing.
- All nylon construction resists salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents. (This feature is not assessed by UL certification or testing.)
- UV Resistant.



Material	Nylon 6/6
Certifications	CE Approved as per EN61386
Temperature Rating	-58°F (-50°C) to 275°F (135°C)
IP Rating	IP 66

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[F8560](#) [F8550](#) [F8556](#) [F8552](#) [F8542](#) [F8546](#) [F8548](#) [F8540](#)