




Wiha TiN Coated Insert/Power Bits

The abbreviation TiN stands for Titanium-Nitride, which has a hardness up to 85 HRC. This coating guarantees a high wear and tear resistance.



- Tough, hard torsion quality with very hard TiN coating
- Optimized torsion zone
- High wear resistance

Titanium Coated



741 Phillips TiN Coated Power Bits. 1/4" Hex Drive, Length 2.0"/50mm

Item	+	—	—
No.	Size	mm	lbs.
741 01	1	50	.04
741 05	2	50	.04
741 08	3	50	.04

TiN - Titanium Nitride



715 TORX® TiN Coated Insert Bits, 1/4"

Item	+	—	—
No.	Size	mm	lbs.
715 85	T5	25	.02
715 86	T6	25	.02
715 87	T7	25	.02
715 88	T8	25	.02
715 62	T9	25	.02
715 63	T10	25	.02
715 64	T15	25	.02
715 65	T20	25	.02
715 66	T25	25	.02
715 69	T27	25	.02
715 67	T30	25	.02
715 68	T40	25	.02

TiN - Titanium Nitride



711 Phillips TiN Coated Insert Bits, 1/4"

Item	+	—	—
No.	Size	mm	lbs.
711 21	1	25	.02
711 22	2	25	.02
711 23	3	25	.02

TiN - Titanium Nitride



711 Phillips TiN Coated Insert Bits. 1/4" Hex Drive, Length 2.0"/50mm

Item	+	—	—
No.	Size	mm	lbs.
711 41	1	50	.04
711 42	2	50	.04
711 43	3	50	.04

TiN - Titanium Nitride

Wear Characteristics

Wiha TiN Coated Bit

Wiha Diamond Bit

Wiha Dura Bit



711 96 PokitPak - Phillips TiN Coated Insert Bits In Molded Case -

- Set Includes 6 - 1/4" Insert Bits
- Phillips Sizes: 2 of each - 1, 2, 3
- lbs. .31

Countersink & Drill Bits

High quality HSS steel, ground with radial relief. Universal application in metal, plastic and wood. Guarantees outstanding removal of cuttings, chatter free operation & smooth surface.

High Precision Tool Holder For Countersinks & Drill Bits



Quick release tool holder for Drills, Countersinks & Power bits

714 80 RapidFix Bit Holder

Item	+	—	—	—
No.	Size	Size	mm	Inch
714 80	1/4"	1/4"	60	2.3

90° Countersink Bit - 1/4" Shank



786 HSS 1/4" Drive 90° Countersinks

High quality HSS steel, ground with radial relief. 1/4" hex shank according to DIN 3126 C 6.3.

Item	—	—	—	—
No.	Size	Inch	mm	Inch
786 15	6.3	.26	35	1.38
786 17	8.3	.33	35	1.38
786 19	10.4	.41	35	1.38
786 21	12.4	.49	35	1.38
786 22	16.5	.65	35	1.38
786 24	20.5	.81	35	1.38

1/4" Shank High Speed Drill Bits



780 1/4" Shank Stubby High Speed Drill Bits DIN 3126 C 6.3.

Item	—	—	—	—
No.	Size	Inch	pkg	lbs.
780 02	1/16	1.26	1	.02
780 05	3/32	1.41	1	.02
780 08	1/8	1.57	1	.02
780 11	5/32	1.73	1	.03
780 15	3/16	1.97	1	.03
780 18	1/4	1.97	1	.03