



Part Number: 130040-0003

Ultra-Lock® Single-Ended Cordset, Male - Pigtail, Straight, 4 Poles, Length 0.50m, Nickel (Ni) Plated Brass Shell, PVC Wire Leads

Image not available

Status:	OBsolete
Replacement:	Contact Molex
Series:	130040
Category:	Industrial Cordsets
Overview:	Brad® Mini-Change® Products
Old Part Number:	@WR4006A42M005

Series image - Reference only

Product Environmental Compliance

[EU RoHS](#): ELV and RoHS Compliant



[China RoHS](#):

[REACH SVHC](#): Not Reviewed

[Low-Halogen Status](#): Not Reviewed

Part Detail

General

Status	Obsolete
Category	Industrial Cordsets
Series	130040
Connector End A	Ultra-Lock® (M12)
Connector End B	Pigtail
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	Brad® Mini-Change® Products
Product Name	Mini-Change®
Type	Single Ended
UPC	78172504915

Physical

Cable Diameter	N/A
Cable Length	0.50m
Color - Cable Jacket	Yellow
Coupling Style	Push to Lock
Gender	Male-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Contact	Copper
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	Straight
Poles	4
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	18
Wire/Cable Type	N/A

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	4A
Voltage - Maximum	250V

Material Info

Old Part Number	@WR4006A42M005
-----------------	----------------

Reference - Drawing Numbers

Sales Drawing

SD-130040-005

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)