




Copyright FCI.

D

C

B

A



PC card drilling dimensions(after plating)
(thickness 2.40±0.20mm)

TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24B.GL00
15	39.14	33.32	25.18	24.54	19.18	D15S24B.GL00
25	53.03	47.04	39.12	38.25	33.12	D25S24B.GL00
37	69.32	63.50	55.68	54.71	49.68	D37S24B.GL00

Protection: 4 --> flash AU
6 --> 0.76µ AU

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24B.GL00LF
15	39.14	33.32	25.18	24.54	19.18	D15S24B.GL00LF
25	53.03	47.04	39.12	38.25	33.12	D25S24B.GL00LF
37	69.32	63.50	55.68	54.71	49.68	D37S24B.GL00LF

Protection: 4 --> flash AU
6 --> 0.76µ AU

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS: SEE DRAWING C01-8646-0000

rev	ecn no	dr	date
C	-	-	1996/09/09
D	LS05-001	MPE	2005/03/10
E	LS05-0056	MPE	2005/06/28
F	LS06-0097	LGO	2006/07/29
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302 ✓	tolerance std ISO 406 ISO 1101	projection mm	size A3		Scale 2
TOLERANCES UNLESS OTHERWISE SPECIFIED			ANGULAR 0.XX' ±2°	LINEAR 0.XX ±0.1 0.XXX ±0.1	size A3		ECN LS06-0097	
Dr	LELEON	1992/09/16	Product family		D-SUB		Spec ref -	
Eng	PESSON	1992/09/16	Product family		D-SUB		Spec ref -	
Chr	LEGARE	1992/09/16	Product family		D-SUB		Spec ref -	
Appr	LEGARE	1992/09/16	Product family		D-SUB		Spec ref -	
FCI			title FEMALE CONNECTOR STD EURO		cat no C01-8646-0125		Rev. F	
straight solder type for			customer		sheet 1 of 1			

REV F - 2006-04-17