

800-Series




The 800-Series rotary switches are single pole and AC rated to 6 amps. These switches feature a self-cleaning wiping action and a silver-plated contact system. A nylon actuator and shaft in a metal clad package highlight the construction of this multi-position switch.

Specifications

- Certifications*: UL, CSA
- Dielectric Strength: 1,000V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Steel/Zinc Plate
- Actuator Material: Nylon
- Bushing Material: Brass/Nickel Plate

* Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]



800	-	4	-	BL
SERIES		SWITCH POSITIONS		ACTUATOR COLOR
800 ROTARY 8 POSITION 3A 250VAC 6A 125VAC		2 2 POSITIONS 3 3 POSITIONS 4 4 POSITIONS 5 5 POSITIONS 6 6 POSITIONS 7 7 POSITIONS 8 8 POSITIONS		BL BLACK
		A FIRST POSITION A2 SECOND POSITION A3 THIRD POSITION A4 FOURTH POSITION A5 FIFTH POSITION A6 SIXTH POSITION A7 SEVENTH POSITION A8 EIGHTH POSITION		

NOTES:
Shading indicates standard configurations.
1 Terminal style is a combination solder lug and quick connect.
2 Not necessary when all "ON" positions specified.