

Supplier	Makita			Hitachi	
Model number	D23700	5903RK	5103R	C7U2	C9U2
Input power (W)	1750	1550	2100	1200	2000/1670
No load speed (rpm)	4700	4500	4000	5500	5000
Saw blade diameter (mm)	235	235	270	190	235
Arbor diameter (mm)	30	30	30	30	30
Cutting capacity 90deg (mm)	86	85	100	66	86
Cutting capacity 45deg (mm)	62	64	73	48	65
Weight (kg)	8.4	7.6	9.4	4	6.8
Order code (230V)	135-2893	138-2557	138-2559	No Order Code	No Order Code
Order code (110V)	135-2894	138-2558	138-2560	No Order Code	No Order Code
Price					
each					