

MATERIALS AND FINISHES :




BODY, COUPLING NUT, CRIMP TUBE BRASS  
PLATED NICKEL

CONTACT BERYLLIUM COPPER  
PLATED GOLD (SEE TABLE)


CABLE CONTACT BRASS  
PLATED GOLD

INSULATOR TEFLON


SHRINK TUBE ATUM OR EQUIVALENT




CONTACT





CRIMP TUBE



SHRINK TUBE



NOTE :  
PLACE SHRINK TUBE  
ONTO CABLE PRIOR  
TO INSERTION IN BODY



RECOMMENDED CABLE STRIP  
DIMENSIONS

|                          |             |
|--------------------------|-------------|
| MIL-STD-348A, FIG. 313.1 | INTERFACE   |
| SPECIFICATION            | DESCRIPTION |

|            |              |             |
|------------|--------------|-------------|
| 73216-1982 | 10u"         | ONE PER BAG |
| 73216-1981 | 10u"         | BULK        |
| 73216-1980 | 30u"         | BULK        |
| PART NO.   | CONTACT PLTG | PACKAGING   |

CHG: ADD 73216-1982

EC NO: 2012/01/30  
DRWN:JWIENER  
CHKD:SSS  
APPR:JWIENER  
2012/01/30  
2012/01/31

DESCRIPTION

QUALITY SYMBOLS  
=0  
=0

GENERAL TOLERANCES  
(UNLESS SPECIFIED)

|          | mm     | INCH    |
|----------|--------|---------|
| 4 PLACES | ± .005 | ± .0005 |
| 3 PLACES | ± .005 | ± .0005 |
| 2 PLACES | ± .005 | ± .0005 |
| 1 PLACE  | ± .005 | ± .0005 |

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE  
MUST REMAIN  
WITHIN DIMENSIONS

DIMENSION STYLE  
MM/IN

|             |            |
|-------------|------------|
| DRAWN BY    | DATE       |
| AZR         | 2008/12/01 |
| CHECKED BY  | DATE       |
| SSS         | 2008/12/01 |
| APPROVED BY | DATE       |
| JDW         | 2008/12/01 |

MATERIAL NO.  
SEE NOTE

SIZE  
C

SCALE  
DESIGN UNITS  
METRIC

THIRD ANGLE  
PROJECTION

TITLE  
TNC PLUG STRAIGHT IP68  
FOR RG58 50 OHMS  
TNC-PC, EWR-3829

MOLEX MOLEX INCORPORATED

DOCUMENT NO.  
SD-73216-198

SHEET NO.  
1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX  
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION