


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	1300060277
Status:	Active
Overview:	Brad Mini-Change Connectors
Description:	Mini-Change A-Size Single-Ended Cordset, 3 Poles, Female (Straight) to Pigtail, 16 AWG, PVC Auto Cable, 0.91m (3.0') Length
Replacement Part Number :	http://www.molex.com/molex/search/partSearch?pQuery=&sType=p&query=13000602171300060217 w/differences

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
UL	E152210
General	
Product Family	Industrial Cordsets
Series	130006
Connector End A	Mini-Change
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Mini-Change Connectors
Product Name	Mini-Change
Protocol	N/A
Region	America
Replacement Part Number	1300060217 w/differences
Type	Single Ended
UPC	78678843018
Physical	
Cable Diameter	10.41mm (.410")
Cable Length	0.91m (3.0')
Color - Cable Jacket	Yellow
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Orientation	Straight to Pigtail
Poles	3
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	16
Wire/Cable Type	STOOW
Electrical	
Current - Maximum per Contact	13.0A
Voltage - Maximum	600V
Material Info	
Engineering Number	103000A02F030
Reference - Drawing Numbers	
Sales Drawing	SD-130006-020



EU ELV Not Relevant	
EU RoHS Not Compliant REACH SVHC Contained Per - ED/01/2018 (15 January 2018) Di-(2-ethylhexyl)phthalate (DEHP) Halogen-Free Status Not Low-Halogen For more information, please visit Contact US	China RoHS
China ROHS ELV RoHS Phthalates	50 Image Not Relevant Contained: DBP,DEHP,DEHP,DEHP,BBP

Search Parts in this Series 130006 Series

This document was generated on 02/05/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION