




D




C

B

A



VIEW X
Ansicht X



- NOTES:**
Bemerkungen:
- 1 HOUSING WITHOUT CLIP 928522
Gehäuse ohne Blechverrastung 928522
 - 2 STEEL HOLE 8+0.2 x 15+0.2
Blechausschnitt 8+0.2 x 15+0.2
 - 3 RADII WITHOUT DIMENSIONS 0.5
Unbemäße Radien 0.5
 - 4 ALL SHARP EDGES
Alle scharfen Kanten
- 5 AMP LOGO
AMP Logo
- 6 ORDER NUMBER
Bestell-Nummer
- 7 CAVITY MARKING
Nestmarkierung

ONLY RECOMMENDED CONTACTTABLE / Kontakttable					
0-927884-1	0-927885-1	-	0.5-1.0 FLR	CuSn4	PRE TIN PLATED
0-927884-2	0-927885-2	-	0.5-1.0 FLR	CuZn 30	PRE TIN PLATED
0-926980-2	0-926981-2	-	0.5-1.0 FLK	CuZn 30	PRE TIN PLATED
AMP ORDER NUMBER		SEAL	WIRE RANGE	MATERIAL	FINISH
STRIP FORM		LOOSE PIECE			

(H1)

-	-	-	-	-	-	-	-
-	-	-	-	-	-	-	-
-	-	-	-	-	-	-	-
-	-	-	-	-	-	-	-
-	0-928521-1	H	1	PA 66	NATURAL	CI II PIN HSG., 9POS.	1
CUSTOMER PART NO	AMP PART NO	REV.	PCS.	MATERIAL	SURFACE COLOR	DESCRIPTION	ITEM NO

NOTE: THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING DEPARTMENT SHALL BE ADVISED FOR THE LATEST REVISION. DIVERS ZÄHLENGEZEIGER WIRD SOWAS AM INCORPORATED KONTROLLIERT. ANMERKUNG: DIESE ZEICHNUNG KONTROLLIERT WIRD. FÜR VERÄNDERUNGEN DER ZEICHNUNG KONTROLLIERT WIRD. FÜR VERÄNDERUNGEN DER ZEICHNUNG KONTROLLIERT WIRD.		DRAWN H. Bouda	300C785	AMP Deutschland GmbH D - 63225 Langen			
CHECKED D. Jakobeit		DATE 30OCT95	NAME CI II PIN HSG., 9POS.	RESTRICTED TO NUR FÜR			
DIMENSIONS mm		TOLERANCES UNLESS OTHERWISE SPECIFIED, ALLIGERE TOLERANZEN		SIZE A1			
0.010 0.010 0.010 0.010		0.010 0.010 0.010 0.010		WEIGHT 2.8g			
MATERIAL PA 66		FINISH/SURFACE/FARBE NATURAL		CUSTOMER DRAWING /KUNDENZEICHNUNG			