



[Home](#) > [All DC Axial](#)

DC Axial Fans - 3610VL-05W-B79 Specifications

[Request Quote](#) [See Stores](#)

Part Specifications		
Product Type	DC Axial Fans	
Part Number	3610VL-05W-B79-B00	3610VL-05W-B79-B50
Rated Voltage	24 (V)	24 (V)
Air Flow	96.40 (CFM)	96.40 (CFM)
Current	0.380 (A)	0.380 (A)
Noise	51.0 (dB)	51.0 (dB)
Input Power	9.12 (w)	9.12 (w)
Size [S]	92 (mm)	92 (mm)
Thickness [L]	25.0 (mm)	25.0 (mm)
Speed	5600 (min ⁻¹)	5600 (min ⁻¹)
Static Pressure	0.600 (H2O)	0.600 (H2O)
Termination	Lead	Lead
Bearing Type	Ball	Ball
Lead Wire Count	3	3
Mounting Type	Ribbed	Ribbed
Lead Wire Type	Locked Rotor	Tachometer

3610VL-05W-B79 DC Axial Fans can be an integral part of a cooling solution for your heat-generating applications. Review the part specifications provided to understand how 3610VL-05W-B79 can work with your system. Ready to purchase 3610VL-05W-B79? Explore the inventory currently available through our distributors below. You can also learn about similar DC Axial Fans parts in inventory by following the links provided. Let NMB Technologies Corporation help you find the cooling solutions you need.

Similar Parts Available

Part Number	
3610KL-04W-B49-G00	Part Details >
3610KL-04W-B50-G00	Part Details >
3610KL-04W-B60-D00	Part Details >
3610KL-05W-B50-G00	Part Details >
3610SB-04W-B20-E00	Part Details >
3610SB-04W-B40-E00	Part Details >
3610SB-04W-B50-E00	Part Details >
3610SB-05W-B20-E00	Part Details >
3610SB-05W-B40-E00	Part Details >
3610SB-05W-B50-E00	Part Details >
3610VL-04W-B30-E00	Part Details >
3610VL-04W-B50-E00	Part Details >
3610VL-04W-B70-E00	Part Details >
3610VL-04W-B79-B00	Part Details >
3610VL-04W-B79-B50	Part Details >
3610VL-05W-B30-E00	Part Details >
3610VL-05W-B50-E00	Part Details >
3610VL-05W-B70-E00	Part Details >