

Aven Inc.
4595 Platt Rd.
Ann Arbor, MI 48108
Phone: 734.973.0099
Email: info@aventools.com • Web Address: www.aventools.com

All Categories > Ergo Stainless Steel Cutters > Stainless Steel Cutters > Stainless Steel Pliers > Niptec Cutters > Specialty Cutters > Parallel Action Pliers > Item # 10761



[larger image](#)

Item # 10761, Flat Nose Plier With Wire Cutter

5" Parallel Action Pliers with Wire Cutters

- Serrated Jaws with V-slot
- Maximum Jaw Opening: 10mm (0.4")
- Soft Wire Cutting Capacity: 2.5mm (0.1")
- Overall Length: 125mm (5")
- Jaw Length: 35mm (1.37")
- Jaw Width: 6.4mm (0.25")

Specifications

Maximum Jaw Opening	0.4 in 10 mm
Cutting Capacity	0.1 in 2.5 mm
Overall Length	5 in 125 mm
Jaw Length	1.37 in 35 mm
Jaw Width	0.25 in 6.4 mm
Weight	0.30 lb

[Print](#) [Back](#)