

Search Results

Evaluate

- Advertisements
- PDFHighest Perf..
- FAQ's
- Product Bulletins
- PDFDirect Buria..
- Videos
- WMV-Panduit Comp..

Design a Solution

- Catalog Cut Sheet
- PDFGCE1/01/0 P
- Part Drawings
- DWG-2-D cad for ..
- PDFE Style Grou..
- DWG-3-D cad for ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain

- Installation Instructions
- PDFDirect Buria..

Home > Products Overview > Search Results >

Current refinements (click  to remove) Search Tips


 Text Search: 'GCE250-1/0'

Your search criteria matched only one product, shown below

**GCE250-1/0**



- Wide range-taking ability and multi-conductor design provide flexibility with a minimum number of parts, allowing for conductor to conductor, conductor to rebar, and conductor to ground rod applications
- Designed for the enhanced crimp process using patent pending technology meets IEEE Std 837™ – 2002
- Slotted design allows quick and easy assembly of conductor to connector using Panduit cable ties, included
- Pre-applied conductive antioxidant compound ensures a high quality mechanical and electrical bond, speeding installation
- Color-coded and marked with Panduit die index numbers for proper crimp die selection
- UL 467 Listed and CSA 22.2 Certified for grounding and bonding suitable for direct burial in earth or concrete when crimped with Panduit or industry standard crimping tools and Panduit dies
- Complies with vibration tests per MIL -STD-202G (METHOD 201A)

Part Number	GCE2501/0
RoHS Compliancy Status	Compliant
Part Description	"E" style grounding connector for 1/0 STR– 250 kcmil (70– 120mm <sup>2</sup> ) main and #6 SOL– 1/0 STR tap (16– 50mm <sup>2</sup> ) tap.
CSA Certified	Yes
UL Listed	Yes
Height (In.)	2.18
Height (mm)	55.4
Length (In.)	1.00
Length (mm)	25.4
Width (In.)	1.05
Width (mm)	26.7
Copper Conductor Size Run	1/0 STR– 250 kcmil
Copper Conductor Size Tap	#6 SOL– 1/0 STR
CE Compliant	No
Copper Conductor Size Run (mm <sup>2</sup> )	(70 – 120)
Copper Conductor Size Tap (mm <sup>2</sup> )	(16 – 50)
Copper Lightning Conductor Size Range Run	59.5 kcmil
Ground Rod Size Tap (In.)	—
Panduit Color Code	Black
Panduit Die Index No.	PG25
Pricing Description	Ground "E" Style Connector, 1/0 STR 250 kcmil (70- 120mm <sup>2</sup> ) main and #6 SOL- 1/0 STR tap (16– 50mm <sup>2</sup> ) tap
Rebar Size Run (In.)	3/8 – 1/2, #3– #4
Rebar Size Tap (In.)	—
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.