


Testo 106

General Description

A range of accurate, yet affordable thermometers suitable for checking core temperatures within the Food Industry under the HACCP guidelines or can be used as a low cost general purpose thermometer. The patented topsafe protects the instrument from dirt, impact and splash-water, and the belt/wall holder facilitates easy handling.



- Quick and Accurate core Temperature Measurement
- Optical limit value monitoring
- Audible Alarm (Testo 106-T2 only)
- Wide measuring range -50°C to $+230^{\circ}\text{C}$

Specifications

Measuring range	-50 to $+230^{\circ}\text{C}$
Resolution	0.1°C
Accuracy	$\pm 0.5^{\circ}\text{C}$ (-30 to $+99.9^{\circ}\text{C}$) $\pm 1^{\circ}\text{C}$ or $\pm 1\%$ (remaining range)
Operation Temperature	-20 to $+50^{\circ}\text{C}$
Storage Temperature	-40 to 70°C
Battery type	
Testo 106-T1	2 x Li cell
Testo 106-T2	2 x AAA
Battery Life	Approx. 250 hrs
Probe Tip	$\varnothing 2.2\text{mm}$ (reinforced to 3mm after 15mm)
Warranty	1 Year

Price

Part No	Description	Price
0560.1061	Testo 106	£24.00
0563.1061	Testo 106-T1 Kit With Topsafe case (IP67), protection cap for measuring tip, wall/belt holder	£32.00
0563.1062	Testo 106-T2 Set With audible alarm With Topsafe case (IP67), protection cap for measuring tip, wall/belt holder	£40.00