


Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

Premium D-Sub Cable Assemblies - Fully Populated and Double Shielded

The CS2N Series of D-Sub cable assemblies is our top of the line D-Sub cabling offering. These cables offer the best features for those applications where only the best will do. The bulk cable utilizes 26 AWG stranded conductors with double shielding (copper braid plus aluminum mylar foil) and flexible PVC jacket. Fully molded backshells also have a unique stamped steel internal enclosure that provides the ultimate in shielding performance. Mounting is done via rugged 4-40 thumbscrews that are easy to grip without the need for a screwdriver. Hex nuts on female connectors are removable to expose 4-40 thumbscrews. Color: Light gray.



Premium 9 Pin D-Sub Cables - Molded, Fully Populated and Double Shielded

CS2N9MM-2.5	Premium Molded Cable, DB9 Male / Male, 2.5 ft	15.75	14.49	13.23	11.97	10.71
CS2N9MM-5	Premium Molded Cable, DB9 Male / Male, 5.0 ft	16.75	15.41	14.07	12.73	11.39
CS2N9MM-6	Premium Molded Cable, DB9 Male / Male, 6.0 ft	17.20	15.82	14.45	13.07	11.70
CS2N9MM-10	Premium Molded Cable, DB9 Male / Male, 10.0 ft	19.00	17.48	15.96	14.44	12.92
CS2N9MM-12	Premium Molded Cable, DB9 Male / Male, 12.0 ft	19.90	18.31	16.72	15.12	13.53
CS2N9MM-15	Premium Molded Cable, DB9 Male / Male, 15.0 ft	21.25	19.55	17.85	16.15	14.45
CS2N9MM-25	Premium Molded Cable, DB9 Male / Male, 25.0 ft	25.75	23.69	21.63	19.57	17.51
CS2N9MM-50	Premium Molded Cable, DB9 Male / Male, 50.0 ft	37.00	34.04	31.08	28.12	25.16
CS2N9MF-2.5	Premium Molded Cable, DB9 Male / Female, 2.5 ft	15.75	14.49	13.23	11.97	10.71
CS2N9MF-5	Premium Molded Cable, DB9 Male / Female, 5.0 ft	16.75	15.41	14.07	12.73	11.39
CS2N9MF-6	Premium Molded Cable, DB9 Male / Female, 6.0 ft	17.20	15.82	14.45	13.07	11.70
CS2N9MF-10	Premium Molded Cable, DB9 Male / Female, 10.0 ft	19.00	17.48	15.96	14.44	12.92
CS2N9MF-12	Premium Molded Cable, DB9 Male / Female, 12.0 ft	19.90	18.31	16.72	15.12	13.53
CS2N9MF-15	Premium Molded Cable, DB9 Male / Female, 15.0 ft	21.25	19.55	17.85	16.15	14.45
CS2N9MF-25	Premium Molded Cable, DB9 Male / Female, 25.0 ft	25.75	23.69	21.63	19.57	17.51
CS2N9MF-50	Premium Molded Cable, DB9 Male / Female, 50.0 ft	37.00	34.04	31.08	28.12	25.16

Premium High Density 15-Pin D-Sub Cables - Molded, Fully Populated, Double Shielded

CS2H15MM-2.5	Premium Molded Cable, HD15 Male / Male, 2.5 ft	20.25	18.63	17.01	15.39	13.77
CS2H15MM-5	Premium Molded Cable, HD15 Male / Male, 5.0 ft	21.75	20.01	18.27	16.53	14.79
CS2H15MM-6	Premium Molded Cable, HD15 Male / Male, 6.0 ft	22.40	20.61	18.82	17.02	15.23
CS2H15MM-10	Premium Molded Cable, HD15 Male / Male, 10.0 ft	25.00	23.00	21.00	19.00	17.00
CS2H15MM-12	Premium Molded Cable, HD15 Male / Male, 12.0 ft	26.30	24.20	22.09	19.99	17.88
CS2H15MM-15	Premium Molded Cable, HD15 Male / Male, 15.0 ft	28.25	25.99	23.73	21.47	19.21
CS2H15MM-25	Premium Molded Cable, HD15 Male / Male, 25.0 ft	34.75	31.97	29.19	26.41	23.63
CS2H15MM-50	Premium Molded Cable, HD15 Male / Male, 50.0 ft	51.00	46.92	42.84	38.76	34.68
CS2H15MF-2.5	Premium Molded Cable, HD15 Male / Female, 2.5 ft	20.25	18.63	17.01	15.39	13.77
CS2H15MF-5	Premium Molded Cable, HD15 Male / Female, 5.0 ft	21.75	20.01	18.27	16.53	14.79
CS2H15MF-6	Premium Molded Cable, HD15 Male / Female, 6.0 ft	22.40	20.61	18.82	17.02	15.23
CS2H15MF-10	Premium Molded Cable, HD15 Male / Female, 10.0 ft	25.00	23.00	21.00	19.00	17.00
CS2H15MF-12	Premium Molded Cable, HD15 Male / Female, 12.0 ft	26.30	24.20	22.09	19.99	17.88
CS2H15MF-15	Premium Molded Cable, HD15 Male / Female, 15.0 ft	36.50	33.58	30.66	27.74	24.82
CS2H15MF-25	Premium Molded Cable, HD15 Male / Female, 25.0 ft	34.75	31.97	29.19	26.41	23.63
CS2H15MF-50	Premium Molded Cable, HD15 Male / Female, 50.0 ft	51.00	46.92	42.84	38.76	34.68

Note: Cables utilizing coaxial signal lines are recommended for video monitors. See page 50 for details.

Premium 25 Pin D-Sub Serial Parallel Cables - Molded, Fully Populated, Double Shielded

CS2N25MM-2.5	Premium Molded Cable, DB25 Male / Male, 2.5 ft	25.25	23.23	21.21	19.19	17.17
CS2N25MM-5	Premium Molded Cable, DB25 Male / Male, 5.0 ft	27.50	25.30	23.10	20.90	18.70
CS2N25MM-6	Premium Molded Cable, DB25 Male / Male, 6.0 ft	28.40	26.13	23.86	21.58	19.31
CS2N25MM-10	Premium Molded Cable, DB25 Male / Male, 10.0 ft	32.00	29.44	26.88	24.32	21.76
CS2N25MM-12	Premium Molded Cable, DB25 Male / Male, 12.0 ft	33.80	31.10	28.39	25.69	22.98
CS2N25MM-15	Premium Molded Cable, DB25 Male / Male, 15.0 ft	36.50	33.58	30.66	27.74	24.82
CS2N25MM-25	Premium Molded Cable, DB25 Male / Male, 25.0 ft	45.50	41.86	38.22	34.58	30.94
CS2N25MM-50	Premium Molded Cable, DB25 Male / Male, 50.0 ft	68.00	62.56	57.12	51.68	46.24
CS2N25MF-2.5	Premium Molded Cable, DB25 Male / Female, 2.5 ft	25.25	23.23	21.21	19.19	17.17
CS2N25MF-5	Premium Molded Cable, DB25 Male / Female, 5.0 ft	27.50	25.30	23.10	20.90	18.70
CS2N25MF-6	Premium Molded Cable, DB25 Male / Female, 6.0 ft	28.40	26.13	23.86	21.58	19.31
CS2N25MF-10	Premium Molded Cable, DB25 Male / Female, 10.0 ft	32.00	29.44	26.88	24.32	21.76
CS2N25MF-12	Premium Molded Cable, DB25 Male / Female, 12.0 ft	33.80	31.10	28.39	25.69	22.98
CS2N25MF-15	Premium Molded Cable, DB25 Male / Female, 15.0 ft	36.50	33.58	30.66	27.74	24.82
CS2N25MF-25	Premium Molded Cable, DB25 Male / Female, 25.0 ft	45.50	41.86	38.22	34.58	30.94
CS2N25MF-50	Premium Molded Cable, DB25 Male / Female, 50.0 ft	68.00	62.56	57.12	51.68	46.24

Premium 37 Pin D-Sub Serial Parallel Cables - Molded, Fully Populated, Double Shielded

CS2N37MM-2.5	Premium Molded Cable, DB37 Male / Male, 2.5 ft	43.90	40.39	36.88	33.36	29.85
CS2N37MM-5	Premium Molded Cable, DB37 Male / Male, 5.0 ft	46.75	43.01	39.27	35.53	31.79
CS2N37MM-10	Premium Molded Cable, DB37 Male / Male, 10.0 ft	52.50	48.30	44.10	39.90	35.70
CS2N37MM-15	Premium Molded Cable, DB37 Male / Male, 15.0 ft	58.25	53.59	48.93	44.27	39.61
CS2N37MM-25	Premium Molded Cable, DB37 Male / Male, 25.0 ft	69.75	64.17	58.59	53.01	47.43
CS2N37MM-50	Premium Molded Cable, DB37 Male / Male, 50.0 ft	98.50	90.62	82.74	74.86	66.98
CS2N37MF-2.5	Premium Molded Cable, DB37 Male / Female, 2.5 ft	43.90	40.39	36.88	33.36	29.85
CS2N37MF-5	Premium Molded Cable, DB37 Male / Female, 5.0 ft	46.75	43.01	39.27	35.53	31.79
CS2N37MF-10	Premium Molded Cable, DB37 Male / Female, 10.0 ft	52.50	48.30	44.10	39.90	35.70
CS2N37MF-15	Premium Molded Cable, DB37 Male / Female, 15.0 ft	58.25	53.59	48.93	44.27	39.61
CS2N37MF-25	Premium Molded Cable, DB37 Male / Female, 25.0 ft	69.75	64.17	58.59	53.01	47.43
CS2N37MF-50	Premium Molded Cable, DB37 Male / Female, 50.0 ft	98.50	90.62	82.74	74.86	66.98

