

Multimeter - TESTFOX CC-1 - 1212211

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Current pliers multimeter, for DC and AC voltage measurements, AC and DC measurements, and resistance measurements

Why buy this product

- ✓ They combine the functions of a digital multimeter with those of a current probe
- ✓ Enclosed in compact and practical housing, so ideal for use in cramped conditions
- ✓ All measuring ranges are protected against overload
- ✓ The current probes can be used for voltages of up to 600 V, category III

Key commercial data

Packing unit	0
Minimum order quantity	1
Catalog page	Page 295 (CL2-2011)
GTIN	 4 046356 449809
Custom tariff number	90303100
Country of origin	TAIWAN

Technical data

General

Color	black
Degree of protection	IP30
Voltage supply	2 x micro battery 1.5 V, LR03, AAA
Measuring category	CAT III 300 V / CAT II 600 V
Test certificate	IEC/EN 61010-1, DIN VDE 0411
Display scope	4000 digits

Classifications

eclass

eCl@ss 4.0	27200312
eCl@ss 4.1	27200301
eCl@ss 5.0	27200301
eCl@ss 5.1	27200301

Multimeter - TESTFOX CC-1 - 1212211

Classifications

eclass

eCl@ss 6.0	27200301
eCl@ss 7.0	27200301

etim

ETIM 3.0	EC000069
ETIM 4.0	EC000069

unspsc

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

Approvals

Approvals

VDE approval of drawings / GOST

Ex Approvals

Approvals submitted

Approval details

VDE approval of drawings 

GOST 