



## Wiha Tamper Resistant **TORX®** Insert Bits and Power Bits

### Tamper Resistant Torx®

Made in Germany -  
Production Quality



Impact resistant modified  
CVM tool steel, hardened

High resistant  
to wear and  
tear for a  
long tool life

Suitable for all applications  
Hardness HRC 59-61  
Suitable for both manual and  
machine applications



**SHOP**

#### 701 TR **TORX®** Bits, Tamper Resistant, 1/4"

| Item | No.    | Size | mm | pkg. | lbs. |
|------|--------|------|----|------|------|
|      | 701 27 | T7s  | 25 | 10   | .12  |
|      | 701 28 | T8s  | 25 | 10   | .12  |
|      | 701 29 | T9s  | 25 | 10   | .12  |
|      | 701 35 | T10s | 25 | 10   | .12  |
|      | 701 39 | T15s | 25 | 10   | .12  |
|      | 701 42 | T20s | 25 | 10   | .12  |
|      | 701 48 | T25s | 25 | 10   | .12  |
|      | 701 60 | T27s | 25 | 10   | .13  |
|      | 701 63 | T30s | 25 | 10   | .13  |
|      | 701 68 | T40s | 25 | 10   | .14  |



**SHOP**

#### 701 Tamper Resistant Torx® Insert Bit

Packs, 1" CVM S2 modified tool steel.

| Item | No.    | Size | mm | lbs. | 2 Bit Pack |
|------|--------|------|----|------|------------|
|      | 701 50 | T7s  | 25 | .03  |            |
|      | 701 51 | T8s  | 25 | .03  |            |
|      | 701 52 | T9s  | 25 | .03  |            |
|      | 701 53 | T10s | 25 | .03  |            |
|      | 701 54 | T15s | 25 | .03  |            |
|      | 701 55 | T20s | 25 | .03  |            |
|      | 701 56 | T25s | 25 | .03  |            |
|      | 701 57 | T27s | 25 | .03  |            |
|      | 701 58 | T30s | 25 | .03  |            |
|      | 701 59 | T40s | 25 | .03  |            |



**SHOP**

#### 705 **TORX®** Power Bits, Tamper Resistant, 1/4" Hex Drive, Length 2.0"/50mm

| Item | No.    | Size | mm | pkg. | lbs. |
|------|--------|------|----|------|------|
|      | 705 07 | T7s  | 50 | 10   | .18  |
|      | 705 08 | T8s  | 50 | 10   | .18  |
|      | 705 09 | T9s  | 50 | 10   | .18  |
|      | 705 10 | T10s | 50 | 10   | .19  |
|      | 705 15 | T15s | 50 | 10   | .19  |
|      | 705 20 | T20s | 50 | 10   | .21  |
|      | 705 25 | T25s | 50 | 10   | .23  |
|      | 705 27 | T27s | 50 | 10   | .23  |
|      | 705 30 | T30s | 50 | 10   | .23  |
|      | 705 40 | T40s | 50 | 10   | .23  |
|      | 705 45 | T45s | 50 | 10   | .33  |
|      | 705 50 | T50s | 50 | 10   | .37  |
|      | 705 55 | T55s | 50 | 10   | .37  |



**SHOP**

#### 725 TR **TORX®** Bits, Tamper Resistant, 5/16"

| Item | No.    | Size | mm | pkg. | lbs. |
|------|--------|------|----|------|------|
|      | 725 42 | T40s | 35 | 10   | .28  |
|      | 725 47 | T45s | 35 | 10   | .32  |
|      | 725 52 | T50s | 35 | 10   | .34  |
|      | 725 57 | T55s | 35 | 10   | .52  |



**SHOP**

#### 725 TR **TORX®** Bits, Tamper Resistant, 5/16" 2 Bit Pack

| Item | No.    | Size | mm | lbs. | 2 Bit Pack |
|------|--------|------|----|------|------------|
|      | 725 62 | T40s | 35 | .28  |            |
|      | 725 63 | T45s | 35 | .29  |            |
|      | 725 64 | T50s | 35 | .30  |            |
|      | 725 67 | T55s | 35 | .32  |            |



**SHOP**

#### 705 Tamper Resistant **TORX®** Power Bit Packs, 2"

| Item | No.    | Size | mm | lbs. | 2 Bit Pack |
|------|--------|------|----|------|------------|
|      | 705 56 | T7s  | 50 | .07  |            |
|      | 705 57 | T8s  | 50 | .07  |            |
|      | 705 58 | T9s  | 50 | .07  |            |
|      | 705 59 | T10s | 50 | .07  |            |
|      | 705 60 | T15s | 50 | .07  |            |
|      | 705 61 | T20s | 50 | .07  |            |
|      | 705 62 | T25s | 50 | .07  |            |
|      | 705 63 | T27s | 50 | .07  |            |
|      | 705 64 | T30s | 50 | .07  |            |
|      | 705 65 | T40s | 50 | .07  |            |
|      | 705 66 | T45s | 50 | .07  |            |
|      | 705 67 | T50s | 50 | .07  |            |
|      | 705 68 | T55s | 50 | .07  |            |

## Torx® Profiles



Torx®



Security  
Torx®



TorxPlus®



Security  
TorxPlus®



Ball End  
Torx®

## Wiha Tamper Resistant **TORXPlus®** Insert Bit



**SHOP**

#### 716 **TORXPlus®** Security Insert Bits, 1/4" Hex, 1" OAL

| Item | No.    | Size  | mm | pkg. | lbs. |
|------|--------|-------|----|------|------|
|      | 716 48 | IPR8  | 25 | 1    | .11  |
|      | 716 50 | IPR10 | 25 | 1    | .11  |
|      | 716 52 | IPR15 | 25 | 1    | .11  |
|      | 716 54 | IPR20 | 25 | 1    | .12  |
|      | 716 56 | IPR25 | 25 | 1    | .13  |
|      | 716 57 | IPR27 | 25 | 1    | .13  |
|      | 716 58 | IPR30 | 25 | 1    | .14  |
|      | 716 60 | IPR40 | 25 | 1    | .14  |