






DATE	ECO NO	DESCRIPTION	BY
Mar 31 1993	CDN 93015		A.K
	DCN 93025	Revise	A.K



Performance.

1. Insulation Resistance : 1000 M Ω min. at 500V.D.C
2. Dielectric Withstanding Voltage : 600 V.A.C (RMS)
3. Contact Resistance : 30 m Ω max. at 20 mV max.
4. Temperature Range : -40°C ~ +150°C

④	CONTACT- (2)	Be Cu	10	PLATING : Au
③	CONTACT- (1)	Be Cu	10	PLATING : Au
②	BASE-20P	PEI	1	COLOR : BLACK
①	COVER-20P	PEI	1	COLOR : BLACK
P.NO	PART DESCRIPTION	MATERIAL	QTY	NOTE
GENERAL TOLERANCES ±0.3 (±.012)				
UNIT mm (in.)	SCALE 2/1	ANGLE 3rd.	 WELLS JAPAN LIMITED ウェルズ・ジャパン株式会社 TITLE SOP 20P SOCKET DWG NO. 652D0202211	
DRAWN	/	/		
CHECKED	/	/		
APPROVED	/	/		