

## Wiha Cabinet Tip Screwdrivers



SHOP

**186 Slotted Cabinet Tip Screwdriver, With Wiha-Square Handle**

Blade chrome-vanadium-molybdenum steel, hardened, nickel-plated. Tip parallel to shaft. Series includes extra long dimensions for screws in difficult to reach locations. Wiha-square handle cellulose-acetate, impact resistant.

| Item   | 1    | 2    | 3   | 4    | 5    | 6    | 7   | 8    | 9    | 10   |
|--------|------|------|-----|------|------|------|-----|------|------|------|
| No.    | mm   | Inch | mm  | Inch | mm   | Inch | mm  | Inch | lbs. | pkg. |
| 186 01 | 2.0  | .08  | 40  | 1.6  | 0.40 | .02  | 100 | 4.0  | .02  | 10   |
| 186 03 | 2.5  | .10  | 50  | 2.0  | 0.40 | .02  | 110 | 4.3  | .02  | 10   |
| 186 06 | 3.0  | .12  | 75  | 3.0  | 0.50 | .02  | 150 | 5.9  | .05  | 10   |
| 186 09 | 3.0  | .12  | 100 | 3.9  | 0.50 | .02  | 175 | 6.9  | .06  | 10   |
| 186 12 | 3.0  | .12  | 150 | 5.9  | 0.50 | .02  | 225 | 8.9  | .06  | 10   |
| 186 15 | 3.0  | .12  | 200 | 8.0  | 0.50 | .02  | 285 | 11.2 | .08  | 10   |
| 186 24 | 4.0  | .16  | 100 | 3.9  | 0.60 | .02  | 185 | 7.3  | .08  | 10   |
| 186 27 | 4.0  | .16  | 150 | 5.9  | 0.60 | .02  | 235 | 9.3  | .10  | 10   |
| 186 30 | 4.0  | .16  | 200 | 8.0  | 0.60 | .02  | 285 | 11.2 | .11  | 10   |
| 186 42 | 5.0  | .20  | 100 | 3.9  | 0.70 | .03  | 195 | 7.7  | .13  | 10   |
| 186 45 | 5.0  | .20  | 150 | 5.9  | 0.70 | .03  | 245 | 9.6  | .15  | 10   |
| 186 48 | 5.0  | .20  | 200 | 8.0  | 0.70 | .03  | 295 | 11.6 | .17  | 10   |
| 186 51 | 5.0  | .20  | 300 | 12.0 | 0.70 | .03  | 395 | 15.6 | .20  | 10   |
| 186 54 | 6.0  | .24  | 100 | 3.9  | 0.90 | .04  | 205 | 8.1  | .19  | 10   |
| 186 57 | 6.0  | .24  | 150 | 5.9  | 0.90 | .04  | 255 | 10.0 | .21  | 10   |
| 186 60 | 6.0  | .24  | 200 | 8.0  | 0.90 | .04  | 305 | 12.0 | .24  | 10   |
| 186 63 | 6.0  | .24  | 300 | 12.0 | 0.90 | .04  | 405 | 15.9 | .29  | 10   |
| 186 72 | 8.0  | .32  | 200 | 8.0  | 1.20 | .05  | 315 | 12.4 | .32  | 10   |
| 186 78 | 8.0  | .32  | 300 | 12.0 | 1.20 | .05  | 415 | 16.3 | .39  | 10   |
| 186 81 | 10.0 | .39  | 200 | 8.0  | 1.60 | .06  | 315 | 12.4 | .37  | 10   |



SHOP

**153 Phillips Screwdriver, With Wiha-Square Handle**

Blade chrome-vanadium-molybdenum steel, hardened, nickel-plated. Wiha-square handle cellulose-acetate, impact resistant.

| Item   | 1    | 2   | 3    | 4   | 5    | 6   | 7    | 8    | 9    | 10 |
|--------|------|-----|------|-----|------|-----|------|------|------|----|
| No.    | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |    |
| 153 05 | 0    | 60  | 2.4  | 3.0 | .12  | 135 | 5.3  | .05  | 10   |    |
| 153 10 | 1    | 80  | 3.1  | 4.5 | .18  | 175 | 6.9  | .11  | 10   |    |
| 153 15 | 1    | 200 | 8.0  | 4.5 | .18  | 295 | 11.6 | .15  | 10   |    |
| 153 25 | 2    | 100 | 3.9  | 6.0 | .24  | 205 | 8.1  | .18  | 10   |    |
| 153 30 | 2    | 250 | 10.0 | 6.0 | .24  | 355 | 14.0 | .27  | 10   |    |
| 153 35 | 2    | 350 | 13.7 | 6.0 | .24  | 455 | 17.8 | .33  | 10   |    |
| 153 40 | 3    | 150 | 5.9  | 8.0 | .32  | 265 | 10.4 | .33  | 10   |    |



SHOP

**222 Pozidriv® Screwdriver, With Wiha-Square Handle**

Blade chrome-vanadium-molybdenum steel, hardened, nickel-plated. Wiha-square handle cellulose-acetate, impact resistant.

| Item   | 1    | 2   | 3    | 4   | 5    | 6   | 7    | 8    | 9    | 10 |
|--------|------|-----|------|-----|------|-----|------|------|------|----|
| No.    | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |    |
| 222 20 | 1    | 200 | 8.0  | 4.5 | .17  | 295 | 11.6 | .15  | 10   |    |
| 222 30 | 2    | 250 | 9.8  | 6.0 | .23  | 355 | 13.9 | .27  | 10   |    |

## Wiha Awls Screwdrivers



SHOP

**300 02 Square Reaming Awl, With Plastic Handle**

Blade chrome-vanadium-molybdenum steel, hardened, nickel-plated. Round handle cellulose-acetate, impact resistant.

| Item   | 1   | 2    | 3   | 4    | 5   | 6    | 7    | 8    | 9 | 10 |
|--------|-----|------|-----|------|-----|------|------|------|---|----|
| No.    | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |   |    |
| 300 02 | 6.0 | .236 | 100 | 3.9  | 185 | 7.3  | .15  | 10   |   |    |



SHOP

**301 02 Round Awl, With Plastic Handle**

Blade chrome-vanadium-molybdenum steel, hardened, nickel-plated. Plastic handle cellulose-acetate, impact resistant.

| Item   | 1   | 2    | 3   | 4    | 5   | 6    | 7    | 8    | 9 | 10 |
|--------|-----|------|-----|------|-----|------|------|------|---|----|
| No.    | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |   |    |
| 301 02 | 6.0 | .236 | 100 | 4.0  | 185 | 7.3  | .15  | 10   |   |    |

## Wiha Offset Screwdrivers



SHOP

**161 Phillips Offset Screwdriver, With Handle**

For working in confined spaces. Blade CVM special steel, hardened, hard chromed. Handle high quality plastic, impact resistant.

| Item   | 1     | 2   | 3    | 4    | 5    | 6    | 7    | 8 | 9 | 10 |
|--------|-------|-----|------|------|------|------|------|---|---|----|
| No.    | Size  | mm  | Inch | mm   | Inch | lbs. | pkg. |   |   |    |
| 161 12 | 1 + 2 | 125 | 4.9  | 5.5  | .217 | .08  | 10   |   |   |    |
| 161 34 | 3 + 4 | 200 | 8.0  | 10.0 | .315 | .33  | 10   |   |   |    |

**207 Slotted Offset Screwdriver, With Handle**

| Item   | 1    | 2    | 3   | 4    | 5   | 6    | 7    | 8    | 9 | 10 |
|--------|------|------|-----|------|-----|------|------|------|---|----|
| No.    | mm   | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |   |    |
| 207 00 | 3.5  | 9/64 | 90  | 3.5  | 0.6 | .02  | .02  | 10   |   |    |
| 207 05 | 4.0  | 5/32 | 100 | 3.9  | 0.8 | .03  | .03  | .10  |   |    |
| 207 10 | 5.5  | 7/32 | 125 | 5.0  | 1.0 | .04  | .06  | 10   |   |    |
| 207 15 | 6.5  | 1/4  | 125 | 5.0  | 1.2 | .05  | .07  | 10   |   |    |
| 207 20 | 8.0  | 5/16 | 150 | 5.9  | 1.2 | .05  | .15  | 10   |   |    |
| 207 25 | 10.0 | 3/8  | 175 | 6.9  | 1.6 | .06  | .23  | 10   |   |    |



SHOP

**207 90 5 Pc. Set Slotted & Phillips Offset Screwdrivers**

Set includes the following drivers:

| No.    | lbs. | Slotted: 6.5, 8.0, 10.0 |
|--------|------|-------------------------|
| 207 90 | .86  | Phillips: 1 + 2, 3 + 4  |