











Rating	10A125VAC 6A250VAC 6A 250VAC 16A125VAC 10A250VAC	Mounting Hole 	Circuit Diagram 												
Contact Resistance	50m ohm Max.		Circuit Diagram 												
Insulation Resistance	DC 500V 100M ohm Min.														
Dielectric Strength	AC 1500V 1 minute														
Operation Temperature	-25°C ~ 85°C	<table><tr><th>Thickness</th><th>X</th><th>Y</th></tr><tr><td>0.75...1.25</td><td>19.2-0.1</td><td>22.2+0.1</td></tr><tr><td>1.25...2.0</td><td>19.4-0.1</td><td>22.2+0.1</td></tr><tr><td>2.0...3.0</td><td>19.8-0.1</td><td>22.2+0.1</td></tr></table>	Thickness	X	Y	0.75...1.25	19.2-0.1	22.2+0.1	1.25...2.0	19.4-0.1	22.2+0.1	2.0...3.0	19.8-0.1	22.2+0.1	
Thickness	X	Y													
0.75...1.25	19.2-0.1	22.2+0.1													
1.25...2.0	19.4-0.1	22.2+0.1													
2.0...3.0	19.8-0.1	22.2+0.1													
Switch Function	3P SPST ON-OFF(Neon) 3P SPST ON-OFF(Neon)														



Material:
Frame: Black, Nylon 66 (94-V2)
Actuator: Black, Nylon 66 (94-V2)
Lens: Red Clear, PC (94-V2)
Terminals 1,2,4,5: Silver plated, Copper alloy
Terminals 3,6: Brass alloy
Light: Neon
Hot stamping: None



Tolerances Unless Otherwise Specified ± 0.3

6/7/13	周傑輝	增加SCI刻字和更新安規					
Date	Name	Description				No.	
Drawn	Checked	Approved	SCI BOM No.	1824406	Model Name	ROCKER SWITCH	
周傑輝			Customer No.		Model No.	R13-33PB2B2-02	Rev.
6/7/13	6/7-13	2013.6.7	Unit	mm	 Shin Chin Industrial Co., Ltd.		X1