

NPN General Purpose Transistors by Ascending V_{ce0} (Continued)

Part Type	V_{ce0} (V) Min	V_{cbo} (V) Min	H_{fe}		I_c/V_{ce} (mA/V)	F_t (MHz) Min	Package
			Min	Max			
PN3566	30	40	150	600	10/10	700	TO-92
PN3641	30	60	40	120	150/10	250	TO-92
PN3643	30	60	100	300	150/10	250	TO-92
PN4141	30	60	40	120	150/10	250	TO-92
PN4142	30	60	100	300	150/10	250	TO-92
PN5449	30	50	100	300	50/2.0	100	TO-92
TN2219	30	60	100	300	150/10	50	TO-237
2N1613	32	75	40	120	150/10	60	TO-39
BCW60A	32	32	120	200	2.0/5.0	125	TO-236
BCW65A	32	60	100	250	100/1.0	100	TO-236
MPS6573	35		100	500	10/5.0	300	TO-92
MPS6574	35		100	300	1/5.0	300	TO-92
2N2218A	40	75	40	120	150/10	250	TO-39
2N2219A	40	75	100	300	150/10	300	TO-39
2N2221A	40	75	40	120	150/10	250	TO-18
2N2222A	40	74	100	300	150/10	300	TO-18
2N3109	40	80	100	300	150/1.0	70	TO-39
2N3903	40	60	50	150	10/1.0	250	TO-92
2N3904	40	60	100	300	10/1.0	200	TO-92
2N3946	40	60	59	150	10/1.0	250	TO-18
2N4400	40	60	50	150	150/1.0	200	TO-92
2N4401	40	60	100	300	150/1.0	250	TO-92
2N4424	40	40	180	540	2/4.5		TO-92
2N4944	40	80	40	120	150/1.0	900	TO-92
2N4946	40	80	100	300	150/1.0	900	TO-92
2N697	40	60	40	120	150/10	50	TO-39
BSR14	40	75	100	300	150/10	300	TO-236
BSR17	40	60	50	150	10/1.0	250	TO-236
BSS79B	40	75	40	120	150/10	250	TO-236
BSS79C	40	75	100	300	150/10	250	TO-236
MMBT2218A	40	75	40	120	150/10	250	TO-236
MMBT2219A	40	75	100	300	150/10	300	TO-236
MMBT2221A	40	75	40	120	150/10	250	TO-236
MMBT2222A	40	75	100	300	150/10	300	TO-236
MMBT3569	40	80	100	300	150/10	60	TO-236
MMBT3903	40	60	50	150	10/0.1	250	TO-236
MMBT3904	40	60	100	300	10/0.1	300	TO-236
MMBT3926	40	60	59	150	10/0.1	250	TO-236
MMBT4400	40	60	50	150	150/1.0	200	TO-236
MMBT4401	40	60	100	300	150/1.0	250	TO-236
MMBT420	40		40	400	5/10	125	TO-236
MPS3903	40	60	20		0.1/1.0	200	TO-92
MPS6514	40		150	300	2/10		TO-92
MPS6530	40	60	40	120	100/1.0		TO-92
MPS6531	40	60	90	270	100/1.0		TO-92
MPA10	40		40	400	5/10	50	TO-92
MPA20	40		40	400	5/10	125	TO-92
PN2218A	40	75	40	120	150/10	250	TO-92
PN2219A	40	75	100	300	150/10	300	TO-92
PN2221A	40	75	40	120	150/10	250	TO-92
PN2222A	40	45	100	300	150/10	300	TO-92
PN222A	40	75	100	300	150/10	300	TO-92
PN3567	40	80	40	120	30/1.0	900	TO-92
PN3569	40	80	100	300	150/1.0	900	TO-92