

	13	12	11	10	9	8	7	6	5	4	3	2	1						
J	PART NO.	CIRCUITS	LENGTH ±.01 [.25]	WIDTH ±.004 [.10]	NOTES: 1. SUBSTRATE AND COVERLAY MATERIAL IS .001 [25uM] POLYIMIDE. 2. CONDUCTOR IS 1/2 OZ (.0007) [18uM] COPPER. 3. PLATING IS 2 MICRO INCHES MINIMUM OF HARD GOLD OVER 100 MICRO INCHES MINIMUM OF NICKEL. 4. TAIL ENDS ARE .008 [.20] THICK. 5. JUMPER CABLES ARE SUITABLE FOR USE WITH MOLEX 502598 SERIES CONNECTOR.										J				
	150150223	23	2.00 [50.8]	.283 [7.2]															
	150150423	23	4.00 [101.6]	.283 [7.2]															
	150150623	23	6.00 [152.4]	.283 [7.2]															
I	150150823	23	8.00 [203.2]	.283 [7.2]	I														
	150151023	23	10.00 [254.0]	.283 [7.2]	I														
	150150225	25	2.00 [50.8]	.307 [7.8]	I														
	150150425	25	4.00 [101.6]	.307 [7.8]	I														
H	150150625	25	6.00 [152.4]	.307 [7.8]	H														
	150150825	25	8.00 [203.2]	.307 [7.8]	H														
	150151025	25	10.00 [254.0]	.307 [7.8]	H														
	150150227	27	2.00 [50.8]	.331 [8.4]	H														
G	150150427	27	4.00 [101.6]	.331 [8.4]	G														
	150150627	27	6.00 [152.4]	.331 [8.4]	G														
	150150827	27	8.00 [203.2]	.331 [8.4]	G														
	150151027	27	10.00 [254.0]	.331 [8.4]	G														
F	150150229	29	2.00 [50.8]	.354 [9.0]	F														
	150150429	29	4.00 [101.6]	.354 [9.0]	F														
	150150629	29	6.00 [152.4]	.354 [9.0]	F														
	150150829	29	8.00 [203.2]	.354 [9.0]	F														
E	150151029	29	10.00 [254.0]	.354 [9.0]	E														
	150150233	33	2.00 [50.8]	.403 [10.2]	E														
	150150433	33	4.00 [101.6]	.403 [10.2]	E														
	150150633	33	6.00 [152.4]	.403 [10.2]	E														
D	150150833	33	8.00 [203.2]	.403 [10.2]	D														
	150151033	33	10.00 [254.0]	.403 [10.2]	D														
	150150239	39	2.00 [50.8]	.472 [12.0]	D														
	150150439	39	4.00 [101.6]	.472 [12.0]	D														
C	150150639	39	6.00 [152.4]	.472 [12.0]	C														
	150150839	39	8.00 [203.2]	.472 [12.0]	C														
	150151039	39	10.00 [254.0]	.472 [12.0]	C														
	150150245	45	2.00 [50.8]	.543 [13.8]	C														
B	150150445	45	4.00 [101.6]	.543 [13.8]	B														
	150150645	45	6.00 [152.4]	.543 [13.8]	B														
	150150845	45	8.00 [203.2]	.543 [13.8]	B														
	150151045	45	10.00 [254.0]	.543 [13.8]	B														
A	150150251	51	2.00 [50.8]	.614]15.6]	A														
	150150451	51	4.00 [101.6]	.614]15.6]	A														
	150150651	51	6.00 [152.4]	.614]15.6]	A														
	150150851	51	8.00 [203.2]	.614]15.6]	A														
	150151051	51	10.00 [254.0]	.614]15.6]															
15015 NUMBER OF CIRCUITS LENGTH SERIES NUMBER PART NUMBER CONSTRUCTION					JUMPER END DETAIL 33 CIRCUIT SHOWN FRONT REAR										QUALITY SYMBOL GENERAL TOLERANCES (UNLESS SPECIFIED) DIMENSION STYLE INCH [MM] SCALE NONE DESIGN UNITS METRIC THIRD ANGLE PROJECTION TITLE .3MM PITCH JUMPER CABLES APPROVED BY SFULTON DATE 2011/11/15 MATERIAL NO. SEE CHART SIZE C THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION MOLEX INCORPORATED DOCUMENT NO. SD-15015-001 SHEET NO. 1 OF 1				