



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION , 19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC		DIST		P		ZONE		LTR		REVISIONS		DATE	APPRO
G		14								REVISED & REDRAWN PER 0720-0303-93		7-28-93	BB



METRIC
DIMENSIONS LISTED IN mm [INCHES]

NOTE:
1. WIRE INSULATION DIA 7.87[.310] MAX



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C		DO NOT SCALE PRINT. DIMENSIONS SPECIFIED IN MILLIMETERS TOLERANCES ON: 201.000 2 PLG DEC ± 0.201.000 3 PLG DEC ± 0.201.000 ANGLES ± 0.201.000		DR 7-28-93 S.S. GULDBY		QTY 100		LOOSE PC		324660	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS 1-800-522-6752		PRODUCT INFORMATION CENTER		VOLTAGE RATING: 600 V MAX		CHK 7-28-93 R. HESSEY		PACKAGE TYPE		AMP Incorporated Harrisburg, PA 17105-3608		PART NO	
FOR APPLICATION TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 10.54-16.77mm² [20, 800-33, 100]		MATERIAL COPPER PER ASTM B-152 MILW, COLOR: BLUE		APPRO 7-28-93 M. BLIS		SPICE, BUTT, SINGLE TO SINGLE, TERMINAL, WIRE SIZE: 6 AWG		NAME			
TOOLING INFORMATION 1-800-526-5142		STRANDED		FINISH TIN PLATE PER MIL-T-10727		APPRO 7-28-93 M. BLIS		APPLICATION SPEC		SIZE 00779		CAGE CODE C=324660	
FOR ORDER ENTRY		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE COMPANY ASSUMES NO RESPONSIBILITY FOR CORRECTIONS FOR THE LATEST REVISION.		WEIGHT		SCALE NTS		SHEET 1 OF 1					