



World Leader in Network and Electrical Solutions

[support](#) | [locate distributor](#) | [about panduit](#) | [careers](#) | [worldwide](#)

[Printer Friendly](#)

[HOME](#) | [SOLUTIONS](#) | [RESOURCES](#) | [PRODUCTS](#) | [SERVICES](#) | [LEARNING](#)

[SEARCH](#)

Current refinements (click to remove)

[Search Tips](#)

[Region](#) [USA](#) [Product Family](#) [Pan-Way® LDPH Surface Raceway System](#) [Text Search: 'LDPH10IW6-A'](#)

Your search criteria matched only one product, shown below.



Pan-Way® Type LDPH Surface Raceway is a single channel raceway designed to route, protect and conceal data, voice, video, fiber-optic and/or power cabling.

- UL and CSA rated 600V; meets UL 5A and CSA C22.2 No. 62.1-03 standards; FT4 rated
- Two-piece hinged design allows cables to be laid in
- Tamper resistant
- Factory applied adhesive backing speeds installation
- Terminates using surface mount outlet box solutions or *PANDUIT® Mini-Com®* Surface Mount Boxes

Part Number:	LDPH10IW6-A
RoHS Compliancy Status:	Compliant
Part Description:	Tamper resistant two-piece latching surface raceway. Supplied with pre-punched mounting holes and factory applied adhesive tape. Available in 6 foot, 8 foot, and 10 foot lengths.
Product Type:	Power Rated Raceway
Color:	Off White
CSA 22.2 No.62-93:	Yes
UL5A Listed:	Yes
Length (ft.):	6
Product Length:	6'
Product Size:	10
Raceway Size:	1.52" x .86" (39.0mm x 22.0mm)
Min. Order UOM:	FT

Min. Order Qty.:	6
BOM Qty. (# of Pkgs.)	
Add to My Catalog	
Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.	
legal information privacy policy site map	

Copyright © 1995-2007, PANDUIT CORP. All rights reserved.