

Path: [Home](#) > [Enclosure Index](#) > [ROLEC-HAMMOND Aluminum Product Index](#) > R190 & R191 Series



[click to enlarge](#)



[click to enlarge](#)

Key Features:

- Modern, high quality instrument enclosure
- Material - Aluminum die-cast: GD SI 12 / DIN 1725
- Shallow lid, deep body
- Captive stainless steel lid screws
- Enclosure can be mounted after closing lid
- Integrated 1.7 mm recess in lid for membrane keypads and front panels
- Neoprene oil and petrol resistant - thermoplastic gasket standard. (-40°C up to +120°C)
- Clip-on design covers - to hide mounting & lid screws (plastic - polyoxymethylene) - grey RAL 7040
- Complete with lid captivation devices
- Degree of protection: NEMA 4X, IP67
- Textured polyester powder coat, grey RAL 7040. (can be supplied unpainted on special order)
-  Link here to [photo tables](#) of each part number

Part No.	 Reader File	 AutoCAD .dxf File	 3D Solid Model .igs & .stp files (zipped)	Units	Width	Length	Depth (Including Lid)
					A	B	C
R191-052-000	 752K	 220K	 266K	mm	50	75	33
				inches	1.9	2.9	1.3
R191-054-000	 735K	 216K	 266K	mm	50	100	33
				inches	1.9	3.9	1.3
R191-070-000	 	 	 	mm	70	100	50

	803K	220K	313K	inches	2.7	3.9	1.9
R191-090-000	 1,082K	 648K	 7.78M	mm	90	120	60
				inches	3.5	4.7	2.4
R191-072-000	 691K	 219K	 314K	mm	70	140	50
				inches	2.7	5.5	1.9
R190-110-000	 1,013K	 672K	 7.67M	mm	110	140	60
				inches	4.3	5.5	2.4
R191-092-000	 1,009K	 658K	 7.80M	mm	90	160	60
				inches	3.5	6.3	2.4
R190-130-000	 956K	 735K	 7.71M	mm	130	160	70
				inches	5.1	6.3	2.8
R191-074-000	 687K	 220K	 314K	mm	70	180	50
				inches	2.7	7.1	1.9
R190-150-000	 932K	 726K	 7.67M	mm	150	180	60
				inches	5.9	7.1	2.4
R191-150-000	 1,465K	 651K	 7.80M	mm	150	180	90
				inches	5.9	7.1	3.5
R190-112-000	 929K	 715K	 7.66M	mm	110	200	60
				inches	4.3	7.9	2.4
R190-170-000	 909K	 717K	 7.59M	mm	170	200	60
				inches	6.7	7.9	2.4
R191-170-000	 910K	 646K	 7.74M	mm	170	200	90
				inches	6.7	7.9	3.5
R190-132-000	 886K	 725K	 7.67M	mm	130	220	70
				inches	5.1	8.7	2.8
R191-200-100	 916K	 267K	 1.32M	mm	200	230	120
				inches	7.9	9.1	4.7
R191-094-000	 640K	 242K	 386K	mm	90	250	60
				inches	3.5	9.8	2.4
R190-152-000	 879K	 726K	 7.57M	mm	150	260	60
				inches	5.9	10.2	2.4
R191-152-000	 864K	 655K	 7.70M	mm	150	260	90
				inches	5.9	10.2	3.5
R190-172-000	 865K	 720K	 7.51M	mm	170	280	60
				inches	6.7	11	2.4

R191-172-000	 866K	 638K	 7.67M	mm	170	280	90
				inches	6.7	11	3.5
R191-202-100	 668K	 193K	 437K	mm	200	330	120
				inches	7.9	13.0	4.7



Link here to [photo tables](#) of each part number

Features (by photos):



click to enlarge

Snap in design covers
hide both lid screws and
installation holes




click to enlarge

Includes optional use lid
captivation straps



click to enlarge

Enclosure can be installed
after closing lid



click to enlarge

Dual channel construction
Mounting holes accessible
with lid closed. All holes
outside of gasket seal.

Exactly what you are looking for???

Link to our stocking distributors - most have "on-line" pricing, stock check
and ordering!!!

Our Distributors

[Order from your favorite distributor](#)

[Home](#) | [Products](#) | [Distributors](#) | [Technical](#) | [Contact Us](#) | [Other Options](#)

Copyright; © 2002-2010 Hammond Mfg Co Inc

URL: <http://www.hammondmfg.com>