


Dimensions: mm (In.)

**Mechanical Specifications:**

- Operating Life: 300,000 cycles min.
- Operating Temperature: -25°C to +70°C

Electrical Specifications:

- Rating: 50mA / 12VDC
- Contact Resistance: 100m Ω max.
- Insulation Resistance: 100M Ω min.
- Dielectric Strength: 250VAC for 1 minute

Note:

- RoHS Compliant and process compatible with 260° solder

Tactile Switch
101-TS6111T1605BC-EV

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-TS6111T1605BC-EV](#)