



|           |                                     |          |                                         |           |         |
|-----------|-------------------------------------|----------|-----------------------------------------|-----------|---------|
| PART NAME | NEMA 4X DIE CAST ALUMINUM ENCLOSURE | PART No. | AN-1307, AN-1307-G, AN-2807 & AN-2807-B | REV. DATE | 2-11-09 |
|-----------|-------------------------------------|----------|-----------------------------------------|-----------|---------|




MATERIAL: ALUMINUM ALLOY #ADC-12


FINISH: NATURAL (NO SUFFIX)  
GRAY (SUFFIX -G)  
SMOOTH BLACK (SUFFIX -B)

NOTES:


- 1) SIX (6) M4 x 20mm (0.787") LG. SCREWS SUPPLIED FOR ASSEMBLY OF COVER TO BODY.
- 2) ALL HOLE DIAMETERS HAVE  $\pm 0.005$  TOLERANCE  
ALL OTHER DIMENSIONS HAVE  $\pm 0.015$  TOLERANCE



BODY



COVER



PART NO. AN-2807 & AN-2807-B  
ARE SUPPLIED WITH A WELDED  
ON MOUNTING BRACKET ONLY.