




-

Technical drawing of a mechanical part with the following dimensions and tolerances:

- Overall width: 21.08 [+.830]
- Overall height: 12.83 ± 0.38 [+.505 ± .015]
- Distance from top edge to center of left hole: 2.54 [+.100]
- Distance from center of left hole to center of middle hole: 7.37 [+.290]
- Distance from center of middle hole to center of right hole: 6.35 [+.250]
- Distance from center of right hole to right edge: 6.35 [+.250]
- Left hole diameter: Ø3.81 [+.150] 2 PLC
- Middle hole diameter: Ø1.52 ± 0.08 [+.060 ± .003] 2 PLC
- Right hole diameter: Ø1.52 ± 0.08 [+.060 ± .003] 2 PLC

METRIC

PH BRZ GOLD		3	NYLON UL 94V-0	2-350942-0
PH BRZ TIN			NYLON UL 94V-0	1-350942-0
CONTACT			HOUSING	PART NO
OWN B. LEWIS		4-30-98	AMP Incorporated	
CHR B. SWING		4-30-98	Harrisburg, PA 17105-3608	
APD K. CORLE		4-30-98	NAME	
PRODUCT SPEC		PIN HEADER ASSEMBLY		
APPLICATION SPEC		RIGHT ANGLE MOUNT, 2 POSITION,		
WEIGHT -		UNIVERSAL MATE-N-LOK™		
		SIZE	CAGE CODE	DRAWING NO
		A1	00779	C-350942
				RESTRICTED TO
CUSTOMER DRAWING		SCALE	SHEET	OF
		4:1	1	REV