




Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



NOTES:

- TUSONIX STANDARD PART NUMBER: 4101-000.
TUSONIX RoHS COMPLIANT PART NUMBER: 4101-000 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
- RoHS COMPLIANT PART MARKED WITH GREEN DOT FOR IDENTIFICATION.

| MIN. CAP. (pF) | WORKING VOLTAGE (WVdc) | | CURRENT Idc. | I.R. MIN. @ 100 (VDC.) | DWV (VDC) | MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220 | | | |
|----------------|------------------------|-------|--------------|------------------------|-----------|---|---------|-------|--------|
| | 85°C | 125°C | | | | 10 MHz | 100 MHz | 1 GHz | 10 GHz |
| 1750 | 250 | 125 | 10 A | 10 G | 500 | 5 | 35 | 50 | 50 |

| | | |
|--|----------------------------|--|
| REVISION RECORD | 0 | Original Release C.O. |
| | 1 | WAS SK 6644-080-S. LE 1-13-84 |
| | 2 | DIM'S & TOL'S REV'D. RELEASED. L.E. 1-8-85 |
| | C.O.1653 | CURRENT UNIT "A" ADDED L.E. 8-20-85 |
| | 2595 | RDN. TO COMP. FMT. S.M. 07-19-00 |
| | 20000914-3-03 | DIM. .145 TOL WAS ±.018. ADDED IR, DWV & CIRCUIT. S.M.11-05-04 |
| 20041105-1-01 | ADDED NOTES. S.M. 03-14-05 | |
| 20050314-3-01 | | |
| --TOLERANCES-- Unless Otherwise Specified | | Title EYELET STYLE EMI FILTER |
| DECIMAL ± .015 [0.38] | | |
| ANGLES ± | | Drawn S.M. 07-19-00 Scale 4 X |
| TUSONIX TUCSON, ARIZONA | | Approved T.C. 07-19-00 |
| | | A 4101-000 |

X-2015 Rev-0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix:](#)

[4101-000LF](#)