


REV.	DATE	DESCRIPTION
NC	11/21/97	INITIAL RELEASE
A	05/01/04	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND DO NOT DISTURB DIMENSIONS ONLY.	APPROVALS	DATE	Amphenol Connex				
8					UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:	DRAWN	G.R.S.	05/01/04	PART DESCRIPTION			
7					0.5 - .8mm ± 0.20mm	CHECKED			N MALE TO BNC FEMALE ADAPTER			
6					B - .50mm ± 0.40mm	ISSUED			PART NO. 242121			
5					SØ - 1.20mm ± 0.10mm							
4	CONTACT BODY	BRASS	NICKEL	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:	SHEET	1	OF 1				
3	CONTACT PIN	PHOS. BRONZE	GOLD	1	.020 - .315 = ± 0.007"				DWG. NO. 242121.DWG			
2	INSULATOR	TEFLON	NATURAL	1	.315 - 1.180 = ± 0.016"				REV. A			
1	BODY	BRASS	NICKEL	1	1.180 - 4.724 = ± 0.020"				SIZE A			
	DESCRIPTION	MATERIAL	FINISH	QTY	DO NOT SCALE DRAWING	CAD FILE	C:/242/242121.DWG		SCALE NA			