

# Wireless Ethernet Port Adapter



## Product Brief RBEPA and RWEPA

The connectBlue Rugged Bluetooth Ethernet Port Adapter (RBEPA) and Rugged Wireless LAN Ethernet Port Adapter (RWEPA) available with a Bluetooth or a Wireless LAN 802.11b/g interface. The Wireless Ethernet Port Adapters are especially well-suited for mobile, rotating and temporary installations where there is a need for replacing the Ethernet cable with a robust and maintenance-free wireless connection. Further, the products are called "Intelligent antennas™" thanks to the ease of use and cost efficiency of the installation and configuration. Another unique feature of the RBEPA and RWEPA is the Low Emission Mode™ which solves potential interference disturbances between Bluetooth and Wireless LAN that is not handled by the Bluetooth implementation of Adaptive Frequency Hopping.

The Wireless Ethernet Port Adapters are part of the connectBlue product range of Wireless Products in industrial housings.

### KEY FEATURES

- Wireless LAN 802.11b/g or Bluetooth
- Unique method to handle interference disturbances without damage to the Bluetooth conformity or the interoperability with other devices
- Built in antenna with an unique half globe radio coverage pattern making installation easy and cost efficient
- Easy configuration either via "button-push" method or via Web configuration pages
- OEM versions for integration in other devices available on request

## NETWORK COMMUNICATION

Ethernet Interface: 10/100BASE-T with automatic MDI/MDIX cross-over  
IP  
TCP  
UDP  
LLDP  
HTTP  
ARP  
DHCP Client / Server  
DNS support  
SNMP  
User management and access control

## WIRELESS INTERFERENCE SOLUTION

Bluetooth Adaptive Frequency Hopping  
connectBlue Low Emission Mode™

## WIRELESS INTERFACE

Bluetooth Support:  
Bluetooth version 2.0 (Qualified and Listed as Product)

- Supported Bluetooth Profiles: Generic Access Profile (GAP), Personal Area Networking Profile (PANU, NAP)
- Class I (range up to 400 m)

Wireless LAN Support:  
IEEE802.11b/g specification

- Security: Supports WEP64, WEP128, WPA-PSK, WPA2-PSK, TKIP, CCMP (AES), LEAP, PEAP
- Regulatory domain support
- Roaming sequence list
- Range up to 500 m

## INFRASTRUCTURE MODES

Managed / Infrastructure (BSS)  
Unmanaged / Ad-hoc (IBSS)

## CONFIGURATION

Simple, push the button method & Web based configuration  
SNMP  
AT commands for advanced setup  
Profinet optimizations

## EXTERNAL INPUT

9-30 V to trigger configurable event, e.g. roaming

## POWER

9-30 VDC  
OEM\*: 3.3 VDC

## HOUSING

IP65 Classed plastic housing  
Easily accessed mounting holes

## DIMENSIONS

91x66x36.2mm  
OEM\*: 81x60x20mm

*\*OEM version available upon request*

## POSSIBLE USE CASES

Bluetooth:

- Point-to-point Ethernet cable replacement
- Part of a Multipoint setup with a NAP device

Wireless LAN:

- Point-to-point Ethernet cable replacement (both in Ad-Hoc and Infrastructure mode)
- Wireless LAN client adapter in an Infrastructure setup
- Point-to-multipoint cable replacement (in progress)

## TYPE APPROVALS

R&TTE (Europe)  
FCC/CFR 47 part 15  
IC (Industrie Canada)

## ENVIRONMENTAL

Operating temperature: -30 to +65 °C  
Storage temperature: -40 to +85°C

## CERTIFICATIONS AND COMPLIANCE

**R&TTE Directive 1999/5/EC**  
EN 300 328 V1.7.1 (2006-10)  
EN 301 489-1 V1.8.1 (2008-04)  
EN 301 489-17 V1.3.2 (2007-06)

## EMC

EN 61000-6-2 (2005)

## Safety Compliance

EN 60950-1:2001 and/or IEC 60950-1:2001 (1st Edition)  
EN 60950-1/A11:2004 + Corrigendum:2004

**Bluetooth version only:**  
**1999/519/EC Council Recommendation**  
EN 50401 (2006)

**Wireless LAN version only:**  
EN 50371 (2002) for the health requirements

## ORDER NUMBERS

### cB-RBEPai-02-A

Rugged Bluetooth Ethernet Port Adapter Complete kit  
Includes: cB-RBEPai-02 unit, 12VDC power adapter with M12 connector and EU plug, UK+US power plug converters, Ethernet cable with RJ45 and M12 connector

### cB-RBEPai-02-0

Rugged Bluetooth Ethernet Port Adapter with internal antenna. Bulk packaged without accessories.

### cB-RWEPAgi-02-A

Rugged Wireless LAN Ethernet Port Adapter Complete kit  
Includes: cB-RBEPai-02 unit, 12VDC power adapter with M12 connector and EU plug, UK+US power plug converters, Ethernet cable with RJ45 and M12 connector

### cB-RWEPAgi-02-0

Rugged Wireless LAN Ethernet Port Adapter with internal antenna

**connectBlue™**

*The strongest connection in a wireless world*

HEAD OFFICE: connectBlue AB | Norra Vallgatan 64 3V | SE-211 22 Malmö | Sweden | Phone +46 40-6307100 | Fax +46 40-237137  
US OFFICE: connectBlue Inc. | 1460 N. Sandburg Terrace, Suite 2412 | Chicago, IL 60610 | USA | Phone +1 312 927 5859 | Fax +1 312 277 3209  
GERMAN OFFICE: connectBlue GmbH | Raiffeisenstrasse 19 | DE-85276 Pfaffenhofen | Germany | Phone +49 8441 786 4160 | Fax +49 8441 786 4161  
info@connectblue.com | us-info@connectblue.com | www.connectblue.com

Printed in Sweden. ©2010 connectBlue AB. All rights reserved. All specifications are subject to change without notice. The connectBlue word mark and logo are owned by connectBlue AB. The Bluetooth word mark and logos are owned by the Bluetooth SIG, Inc. and any use of such marks by connectBlue is under license.