



Connectors, reducers and couplers

• HG-Y Y-Connector, IP66

Features and Benefits

- Fast fit Y-connector
- Branches reduce conduit size
- High pull-off strength
- Highly resistant to solvents and oils
- Free of halogen, sulphur and phosphorus

Technical Table

Article-No.	Type	Entry nominal diameter	Exit nominal diameter	Pack Cont.
166-25801	HG16-Y13	16	13	5
166-25802	HG21-Y16	21	16	3
166-25803	HG28-Y21	28	21	3
166-25804	HG34-Y28	34	28	2

All dimensions in mm. Subject to technical changes.

Colour grey available on request.



HelaGuard HG-Y, Y-Connector, IP66.

Material Data

Material	Polyamide 6.6 (PA66)
Colour	Black (BK)
Operating Temperature	-50 °C to +135 °C
Flammability	UL94 V2



• HGL-Y Y-Connector, IP68

Fulfills IP66, IP67, IP68 and IP69k.

Features and Benefits

- Fast fit Y-connector
- Branches reduce conduit size
- High pull-off strength
- Highly resistant to solvents and oils
- Free of halogen, sulphur and phosphorus

Technical Table

Article-No.	Type	Entry nominal diameter	Exit nominal diameter	Pack Cont.
166-25901	HGL16-Y13	16	13	5
166-25902	HGL21-Y16	21	16	3
166-25903	HGL28-Y21	28	21	3
166-25904	HGL34-Y28	34	28	2

All dimensions in mm. Subject to technical changes.

Colour grey available on request.



HelaGuard HGL-Y, Y-Connector with conduit seals.



Please note! Not all products listed on this page may have this approval.
For product specific approvals please refer to the Appendix.