






## Dimensions: mm (in.)



Mouser Stock No.	Button Color
103-7049-EV	Orange
103-7050-EV	Red

## Electrical Specifications:

- Rating: 16A / 125VAC 1 / 8HP  
10A / 250VAC 1 / 3HP
- Contact Resistance: 50m  $\Omega$  max.
- Insulation Resistance: 500 VDC 100M  $\Omega$  min.
- Dielectric Strength: 1500 VAC 1 minute

## Mechanical Specifications:

- Operating temperature:  $-25^{\circ} \sim 85^{\circ}$
- Circuit: 3P SPST On-Off
- Neon Lamps: 110VAC

## Materials:

- Frame: Nylon #66, Black
- Neon:  $\phi 4$ , NE-2C
- Resistor: 1/8W, 33k $\Omega$

## Note:

- RoHS Compliant

**Illuminated Rocker Switches**  
103-7049-EV, 103-7050-EV

**Mountain**  
**Switch**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[103-7049-EV](#) [103-7050-EV](#)