





Crimphousing 1,25 mm		Series	425
		pitch	1,25
		Rated current	1,0 A
		Rated voltage	100 V _{RMS} / V _{DC}
		Withstand voltage	500 V _{RMS} for 1 minute
		Material contact	Copper alloy
		Material insulator	Thermoplast UL94V-0
		Operating temperature	-40°C to +105°C
All dimensions in mm.		max. pincount	015
Variation	Contact	Series	606
	1	AWG 28 - 32	
		 Plating: T = Sn Packaging: R = Reel	
		606-1-TX-XR	
		Crimp Tool	454
			
		454-1-01	
		 www.mpe-connector.de	
Order code:		425-1-??-X-KS0	