


TL3265 SERIES TACT SWITCH




APPLICATIONS / MARKETS




Audio / Visual



Computer Peripherals



Consumer Electronics



Instrumentation



Medical Equipment



Telecommunication

RoHS

SPECIFICATIONS

Electrical Rating: 50mA @ 12VDC
Life Expectancy: 500,000 Cycles
Contact Resistance: 100mΩ Max.
Insulation Resistance: 100MΩ Min. at 500VDC
Dielectric Strength: 500VAC for 1 min.
Operating Temperature: -40°C to 85°C
Operating Force: 160 gf
Travel: 0.20mm
Function: SPST, Off-(On), Momentary

FEATURES & BENEFITS

- 500,000 cycle life expectancy
- Multiple cap options
- Surface mount design
- Illumination options

PART NUMBER CONFIGURATOR

Series	Model	LED Option	Contact Material	Cap Option	Cap Color
TL	3265	A	Q	S	CLR
		A - White B - Red R - Green G - Blue Y - Yellow W - White RG - Red/Green bi-color	Q - Silver	S - 5mm Diameter, Round T - 4.7mm Diameter, Round N - No Cap	* CLR - Clear

**All caps are shipped bulk*

Specifications subject to change without notice



E-SWITCH®





www.e-switch.com

800.867.2717

1

TL3265 SERIES TACT SWITCH

BODY DIMENSIONS/ CAP OPTION



S - CAP OPTION



E-SWITCH®

www.e-switch.com





800.867.2717

2

ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS

TL3265 SERIES TACT SWITCH

BODY DIMENSIONS/ CAP OPTION



T - CAP OPTION








E-SWITCH®

www.e-switch.com

800.867.2717

3

BODY DIMENSIONS/ CAP OPTION



ALL TERMINALS TO
BE COPLANNER WITH
0.1 [0.004 in]

N - CAP OPTION