




RECOMMENDED MOUNTING HOLE PATTERN
FOR .063 THICK P.C. BOARD

TIN	3,744	95.10	24	5-641114-4	TIN-LEAD	3,744	95.10	24	2-641114-4
TIN	3,538	97.14	23	5-641114-3	TIN-LEAD	3,538	97.14	23	2-641114-3
TIN	3,326	97.14	22	5-641114-2	TIN-LEAD	3,326	97.14	22	2-641114-2
TIN	3,272	93.21	21	5-641114-1	TIN-LEAD	3,276	93.21	21	2-641114-1
TIN	3,120	79.25	20	5-641114-0	TIN-LEAD	3,120	79.25	20	2-641114-0
TIN	2,964	79.25	19	4-641114-9	TIN-LEAD	2,964	79.25	19	1-641114-9
TIN	2,808	71.32	18	4-641114-8	TIN-LEAD	2,808	71.32	18	1-641114-8
TIN	2,652	67.36	17	4-641114-7	TIN-LEAD	2,652	67.36	17	1-641114-7
TIN	2,496	63.40	16	4-641114-6	TIN-LEAD	2,496	63.40	16	1-641114-6
TIN	2,340	59.44	15	4-641114-5	TIN-LEAD	2,340	59.44	15	1-641114-5
TIN	2,184	55.47	14	4-641114-4	TIN-LEAD	2,184	55.47	14	1-641114-4
TIN	2,028	51.51	13	4-641114-3	TIN-LEAD	2,028	51.51	13	1-641114-3
TIN	1,872	47.55	12	4-641114-2	TIN-LEAD	1,872	47.55	12	1-641114-2
TIN	1,716	43.59	11	4-641114-1	TIN-LEAD	1,716	43.59	11	1-641114-1
TIN	1,560	39.62	10	4-641114-0	TIN-LEAD	1,560	39.62	10	1-641114-0
TIN	1,404	35.66	9	3-641114-9	TIN-LEAD	1,404	35.66	9	641114-9
TIN	1,248	31.70	8	3-641114-8	TIN-LEAD	1,248	31.70	8	641114-8
TIN	1,092	27.74	7	3-641114-7	TIN-LEAD	1,092	27.74	7	641114-7
TIN	936	23.77	6	3-641114-6	TIN-LEAD	936	23.77	6	641114-6
TIN	780	19.81	5	3-641114-5	TIN-LEAD	780	19.81	5	641114-5
TIN	624	15.85	4	3-641114-4	TIN-LEAD	624	15.85	4	641114-4
TIN	468	11.89	3	3-641114-3	TIN-LEAD	468	11.89	3	641114-3
TIN	312	7.92	2	3-641114-2	TIN-LEAD	312	7.92	2	641114-2
TIN	FINISH	IN	MM	NUMBER OF PART NUMBER	FINISH	IN	MM	NUMBER OF PART NUMBER	

[illegible]

METRIC

CUSTOMER DRAWING		SCALE	SHEET	OF	REV
		E. 1	1	1	C