

VC-EMV-KV-PG16(9-13/10,5)

Order No.: 1854174

The illustration shows versions Pg16 and Pg21

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1854174>

EMC half screw connection Pg16, for metal housings, consisting of rubber seal, iris spring, cone disks and pressure screw, for size 1 housings, cable shielding range [mm] 6.5-10.5, cable [mm] 9-13

Commercial data

GTIN (EAN)	 4 017918 145767
sales group	D290
Pack	1 pcs.
Customs tariff	85369010
Catalog page information	Page 374 (PC-2009)

Product notesWEEE/RoHS-compliant since:
01/01/2008

<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General data**

Note	Adapter screw connections are available on request for large cable dimensions, from Pg16 to Pg21 and from Pg21 to Pg29
Material, pressure screw	Nickel-plated brass
Seal material	TPE

Wrench size, union nut	24 mm
Thread type on seal side	PG16
External cable diameter	9 mm ... 13 mm
Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C

Certificates / Approvals

Certification GOST

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact
Technical modifications reserved;